

KSP EL30**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSP (Klippon shroud), Protective cap, PVC
Order No.	1736670000
Type	KSP EL30
GTIN (EAN)	4008190956332
Qty.	10 pc(s).
Delivery status	This article will no longer be available in the future.
Available until	2023-07-30

KSP EL30**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Length	130 mm	Length (inches)	5.118 inch
Wall thickness, min.	2 mm	Wall thickness, max.	2 mm
Net weight	34 g		

Temperatures

Operating temperature	-25 °C...70 °C
-----------------------	----------------

General information

Gap, internal dimension B	80 mm	Halogen	No
Hardness (Shore A)	65	Inside diameter D2	30 mm
Material	PVC	O.D.	34 mm
Operating temperature range, max.	70 °C	Operating temperature range, min.	-25 °C
Silicone	No	Thickness	2 mm

Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

KSP EL30

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

