

SKMU M20 K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU PA (plastic locknut), Locknut, M 20, 6 mm, Polyamid 6 (PA6 - GF30)
Order No.	1736930000
Type	SKMU M20 K SW
GTIN (EAN)	4008190956400
Qty.	100 pc(s).

SKMU M20 K SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	6 mm	Height (inches)	0.236 inch
Net weight	1.8 g		

Temperatures

Operating temperature	-40 °C... 100 °C
-----------------------	------------------

General information

AF size 1	26 mm	Cable glands	M 20
External thread	M 20	Halogen	No
Internal thread	M 20	Length of thread	6 mm
Material	Polyamid 6 (PA6 - GF30)	O.D.	30.03 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Silicone	No
Thickness	6 mm	UL 94 flammability rating	HB

Classifications

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9.1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

Approvals

Approvals



ROHS

Conform

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

SKMU M20 K SW

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

