

SKMU M32 K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | |
|------------|---|
| Version | SKMU PA (plastic locknut), Locknut, M 32, 7 mm, Polyamid 6 (PA6 - GF30) |
| Order No. | 1736950000 |
| Type | SKMU M32 K SW |
| GTIN (EAN) | 4008190956424 |
| Qty. | 100 pc(s). |

SKMU M32 K SW**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Height | 7 mm | Height (inches) | 0.276 inch |
| Net weight | 6.37 g | | |

Temperatures

| | |
|-----------------------|------------------|
| Operating temperature | -40 °C... 100 °C |
|-----------------------|------------------|

General information

| | | | |
|-----------------------------------|-------------------------|-----------------------------------|----------|
| AF size 1 | 41 mm | Cable glands | M 32 |
| External thread | M 32 | Halogen | No |
| Internal thread | M 32 | Length of thread | 7 mm |
| Material | Polyamid 6 (PA6 - GF30) | O.D. | 47.36 mm |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Pitch of thread | 1.5 mm | Silicone | No |
| Thickness | 7 mm | UL 94 flammability rating | HB |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000940 | ETIM 7.0 | EC000940 |
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ECLASS 9.0 | 27-14-44-24 | ECLASS 9.1 | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-07 | ECLASS 13.0 | 27-14-08-07 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

SKMU M32 K SW

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

