

**KLBUE 4-13.5 CPF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Thanks to special mounting feet, the product portfolio also includes shield clamping saddles that can be mounted on the C-profiles. The shield is diverted from the shield clamping saddles via the mounting foot to the C-profiles and thus to PE (ground).

**General ordering data**

Version	Clamping yoke, Clamping yoke, Steel
Order No.	<a href="#">1752691001</a>
Type	KLBUE 4-13.5 CPF
GTIN (EAN)	4032248044429
Qty.	10 pc(s).

**KLBUE 4-13.5 CPF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

Depth	31.5 mm	Depth (inches)	1.24 inch
Height	22 mm	Height (inches)	0.866 inch
Width	20.5 mm	Width (inches)	0.807 inch
Mounting dimension - width	19 mm	Net weight	23.1 g

**Temperatures**

Storage temperature	-25 °C...55 °C
---------------------	----------------

**Material data**

Material	Steel	Colour	grey
----------	-------	--------	------

**System specifications**

Version	For a shield connection	Rail	TS 27
---------	-------------------------	------	-------

**Additional technical data**

Explosion-tested version	Yes	Installation advice	Direct mounting
Type of fixing	when screwed in		

**Conductors for clamping (rated connection)**

Cable diameter, max.	13.5 mm	Cable diameter, min.	4 mm
----------------------	---------	----------------------	------

**Dimensions**

Pitch in mm (P)	20 mm
-----------------	-------

**General**

Installation advice	Direct mounting	Rail	TS 27
---------------------	-----------------	------	-------

**Classifications**

ETIM 6.0	EC002020	ETIM 7.0	EC002020
ETIM 8.0	EC002020	ETIM 9.0	EC002020
ECLASS 9.0	27-14-11-50	ECLASS 9.1	27-14-11-50
ECLASS 10.0	27-14-11-50	ECLASS 11.0	27-14-11-50
ECLASS 12.0	27-14-11-50	ECLASS 13.0	27-25-01-20

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Beipackzettel_KLBUE.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**KLBUE 4-13.5 CPF****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Steel**

Steel DIN rails are the most widespread on the market. Among metal DIN rails, they have the lowest shortcircuit protection, similar to stainless steel.

**General ordering data**

Type	TS 27X12.5M/ST/F.ZN	Version
Order No.	<a href="#">1802690000</a>	Terminal rails, Rail, DIN EN 60715, Steel
GTIN (EAN)	4032248257201	
Qty.	2 m	