

CLI TM 20-66**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. The system is particularly suitable for large conductor and cable cross-sections.

Advantages:

- Combination marker for cable and pipe markers
- One size for all diameters above 16 mm²
- Unrestricted combination options
- Closed, permanently attached markers
- Very good legibility

General ordering data

Version	CableLine, Conductor and cable markers, 10 - 317 mm, 66 x 11.3 mm, Transparent
Order No.	1763390000
Type	CLI TM 20-66
GTIN (EAN)	4032248050840
Qty.	50 pc(s).

CLI TM 20-66**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	5 mm	Depth (inches)	0.197 inch
Height	66 mm	Height (inches)	2.598 inch
Width	11.3 mm	Width (inches)	0.445 inch
Net weight	1.3 g		

Temperatures

Operating temperature range	-30...60 °C
-----------------------------	-------------

General data

Colour	Transparent
Halogen	Yes
Material	PVC
Number of markers per combination	1 Component part = Conductor and cable markers
Number of markers per packaging unit	Form of supply Component part
Operating temperature range	-30...60 °C
Operating temperature range, max.	60 °C
Operating temperature range, min.	-30 °C
Recommended industries	Process, Machinery
Type of printing	neutral
UL 94 flammability rating	V-0
Width	11.3 mm

Conductor and cable markers

Conductor O.D.	10 - 317 mm	Conductor O.D., max.	317 mm
Conductor O.D., min.	10 mm	Conductor cross-section, max.	500 mm ²
Conductor cross-section, min.	16 mm ²	Cross-section for connected wire	16 - 500 mm ²
Halogen	Yes		

Classifications

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--

CLI TM 20-66**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****CLI F 2-17,5**

The Weidmüller range of conductor and cable marker products provides users with solutions for a wide variety of applications. The field of application ranges from thin conductors to cables with large outside diameters. The product range includes combination systems with individual tags, transparent sleeves and markers which can be fastened with cable ties.

Open and closed markers, as well as printed or blank markers for individual labelling are available. Weidmüller's halogen-free and low-emission conductor markers are in compliance with European standards as well as with the in-house standards of well-known plant manufacturers.

Markers for conductors and cables - Systems are available for:

- Clipping on pre-printed markers to suit individual labelling requirements
- Labelling with characters from a standard character set
- Combining individual, pre-printed characters to form a character code
- Customer labelling with SMark laser, PrintJet, MCP Plus plotter, MC-Mobilo, laser printer (DIN A4 format), thermal transfer printer or STI pen

A selection of samples can be found in the Weidmüller conductor marker sample bag, order No. 1640420000.

General ordering data

Type	CLI F 2-17.5 WS/GE	Version
Order No.	1764050000	CableLine, Conductor and cable markers, 17.5 x 9 mm, white
GTIN (EAN)	4032248052431	
Qty.	10 pc(s).	

CLI TM 20-66

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

ESO insert tags



General ordering data

Type	ESO 5 S DIN A4 WS	Version
Order No.	1631920000	Terminal markers, Insert markers, 40 x 7 mm, white
GTIN (EAN)	4008190206673	
Qty.	10 pc(s).	

Blank



ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 9/17 K MC NE WS	Version
Order No.	1674760000	ESG, Device markers x 17 mm, PA 66, Colour: white, Self-adhesive
GTIN (EAN)	4008190447649	
Qty.	200 pc(s).	