

**CLI T 3-12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The CLI T sleeve is a high-quality, transparent sleeve for marking conductors and cables with cross-sections up to 75 mm<sup>2</sup>. The CLI T sleeve is available in four lengths so that labelling with long character strings is possible. The transparent sleeve optimally protects the inlay tag against outside influences. As inlay tag the TM-I marker from the MultiCard and MultiMark portfolio be suitable.

- Wider cross-section range per sleeve
- A special flexible bellow profile ensures a wide application range
- Easy insertion of the TM-I tag into the sleeve pocket before or after connecting the conductor
- Available in five lengths
- Not suitable for labelling with P-Ink or STI pen

**General ordering data**

Version	CableLine, Socket x 5 mm, PVC, Colour: Transparent, Conductor O.D.: 8 - 16 mm
Order No.	<a href="#">1764270000</a>
Type	CLI T 3-12
GTIN (EAN)	4032248053339
Qty.	100 pc(s).

**CLI T 3-12****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	19 mm	Depth (inches)	0.748 inch
Height	12 mm	Height (inches)	0.472 inch
Width	5 mm	Width (inches)	0.197 inch
Net weight	0.828 g		

**Temperatures**

Operating temperature range	-30...80 °C
-----------------------------	-------------

**General data**

Colour	Transparent	Material	PVC
Operating temperature range	-30...80 °C	Operating temperature range, max.	80 °C
Operating temperature range, min.	-30 °C	Recommended industries	Transportation, Machinery
Type of printing	neutral	UL 94 flammability rating	V-0
Width	5 mm		

**Conductor and cable markers**

Conductor O.D.	8 - 16 mm	Conductor O.D., max.	16 mm
Conductor O.D., min.	8 mm	Conductor cross-section, max.	75 mm <sup>2</sup>
Conductor cross-section, min.	25 mm <sup>2</sup>	Cross-section for connected wire	25 - 75 mm <sup>2</sup>

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Product Change Notification	<a href="#">PCN Transparent Sleeves_DE</a> <a href="#">PCN Transparent Sleeves_EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>