

VP M50-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	VPMS (blanking plug in brass), Blanking plug, in closed state, M 50, 9 mm, Brass, nickel-plated
Order No.	1777780000
Type	VP M50-MS65
GTIN (EAN)	4032248158058
Qty.	25 pc(s).

VP M50-MS65**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	15 mm	Height (inches)	0.591 inch
Length	15 mm	Length (inches)	0.591 inch
Diameter	54 mm	Wall thickness, min.	0.5 mm
Wall thickness, max.	8 mm	Net weight	69.84 g

Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

General information

Cable glands	metric	Diameter of sealing ring	50 mm
External thread	M 50	Halogen	No
Head diameter	54 mm	Length of thread	9 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Protection degree	IP68 - 5 bar (30 min.)
Sealing	NBR	Silicone	No

Classifications

ETIM 6.0	EC000451	ETIM 7.0	EC000451
ETIM 8.0	EC000451	ETIM 9.0	EC000451
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-33
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-14-08-05	ECLASS 13.0	27-14-08-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	0c0edf9f-b35a-4d1f-b8f0-99d4b22ac203

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

VP M50-MS65

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

