


**KOSF ZT2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Through the use of coding pins, individual coding options ensure trouble-free plug-in connection.

**General ordering data**

Version	Z-series, Coding element, yellow, 2.9 mm
Order No.	<a href="#">1816150000</a>
Type	KOSF ZT2.5
GTIN (EAN)	4032248370726
Qty.	50 pc(s).

**KOSF ZT2.5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	11.25 mm	Depth (inches)	0.443 inch
Height	4.4 mm	Height (inches)	0.173 inch
Width	2.9 mm	Width (inches)	0.114 inch
Net weight	0.2 g		

**Temperatures**

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50
Continuous operating temp., max.	100		

**Material data**

Material	PA 66 GF 30	Colour	yellow
UL 94 flammability rating	HB		

**System specifications**

Version	Coding element
---------	----------------

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Plugged		

**General**

Installation advice	Direct mounting
---------------------	-----------------

**Classifications**

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Engineering Data	<a href="#">Zuken E3.S</a>
User Documentation	<a href="#">StorageConditionsTerminalBlocks</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

### KOSF ZT2.5

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

