

**CBFP 43.5/10 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Fastening of cables or bundles with ties into electrical switchgears and cabinets.

**General ordering data**

Version	Cable ties, 10 x 10 mm, Plastic, 80 N
Order No.	<a href="#">1859410000</a>
Type	CBFP 43.5/10 BK
GTIN (EAN)	4032248412297
Qty.	100 pc(s).

**CBFP 43.5/10 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	2 mm	Depth (inches)	0.079 inch
Height	10 mm	Height (inches)	0.394 inch
Width	10 mm	Width (inches)	0.394 inch
Net weight	1.91 g		

**Temperatures**

Operating temperature range	-40...100 °C
-----------------------------	--------------

**Installation materials**

Diameter of fastening hole	8 mm	For re-opening	No
Material	Plastic	Max. cable tie width	9 mm
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Tensile strength	80 N	Tensile strength (Pound-force)	18 lbf
UL 94 flammability rating	V-2	UV-resistant	No
Version	for wall mounting		

**Classifications**

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ETIM 9.0	EC000046
ECLASS 9.0	27-14-07-02	ECLASS 9.1	27-14-07-02
ECLASS 10.0	27-14-07-02	ECLASS 11.0	27-14-07-02
ECLASS 12.0	27-14-07-02	ECLASS 13.0	27-14-07-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## CBFP 43.5/10 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Dimensional drawing

