

DAE M12 PA LONG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	DAE (ventilation element), Compensating element, straight, M 12, 10 mm, IP66, IP68, IP69K, Polyamide 6
Order No.	1868570000
Type	DAE M12 PA LONG
GTIN (EAN)	4032248440429
Qty.	10 pc(s).

DAE M12 PA LONG**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Height	7.6 mm	Height (inches)	0.299 inch
Length	17.4 mm	Length (inches)	0.685 inch
Wall thickness, min.	0.5 mm	Wall thickness, max.	10 mm
Net weight	1.7 g		

Temperatures

Operating temperature	-40 °C...105 °C
-----------------------	-----------------

General information

Air flow	0.8 l/min at 0.1 bar ΔP , up to 7.6 l/min at 1 bar ΔP	Cable glands	metric
External thread	M 12	Halogen	halogen-free
Inside diameter D2	12 mm	Installation guidelines	See assembly instructions
Length of thread	10 mm	Material	Polyamide 6
O-Ring	NBR	Operating temperature range, max.	105 °C
Operating temperature range, min.	-40 °C	Pitch of thread	1.5 mm
Protection degree	IP66, IP68 (1 m / 60 min), IP69K	Protection degree with GWDR	IP66, IP68, IP69K
Silicone	No	Torque for connecting adapter, max.	0.6 Nm
Torque for connecting adapter, min.	0.4 Nm	UL 94 flammability rating	V-2
Water inlet point	> 1.5 bar		

Classifications

ETIM 6.0	EC000814	ETIM 7.0	EC000814
ETIM 8.0	EC000814	ETIM 9.0	EC000814
ECLASS 9.0	27-14-44-25	ECLASS 9.1	27-14-44-90
ECLASS 10.0	27-14-44-25	ECLASS 11.0	27-14-44-25
ECLASS 12.0	27-18-28-17	ECLASS 13.0	27-18-28-17

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	

DAE M12 PA LONG

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

