

**SCREWTY M8 KO O. SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The Screwty® attachment is suitable for M8 round plug-in connectors, with an outside dimension of the knurled nut of  $10 \pm 0.3$  mm. The tightening torque is 0.5-0.6 Nm.

**General ordering data**

Version	Cable gland tool adapter for moulded M8 lines
Order No.	<a href="#">1900110000</a>
Type	SCREWTY M8 KO O. SD
GTIN (EAN)	4032248409969
Qty.	1 pc(s).
Packaging	Plastic bag

**SCREWTY M8 KO O. SD****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	13 g
------------	------

**Screwing tools**

Connection thread	M8	Size	10 mm
-------------------	----	------	-------

**Classifications**

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>