

**SAIH-4X0,34(PUR)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Weidmüller offers a large and comprehensive range of sensor-actuator cables. We provide both, sensor cables as well as bus and valve cables of various sizes and lengths. If you cannot find a specific product or a product in the desired length, just contact us.

**General ordering data**

|            |  |
|------------|--|
| Version    | Sensor/actuator line, Number of poles : 4, Shielded: No, Sheath material: PUR, Halogen: No |
| Order No.  | <a href="#">1902130000</a>   |
| Type       | SAIH-4X0,34(PUR)   |
| GTIN (EAN) | 4032248515875  |
| Qty.       | 100 m  |

## SAIH-4X0,34(PUR)

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 29.83 g |
|------------|---------|

## Technical specifications for cable

|  |                                  |                               |   |
|--|----------------------------------|-------------------------------|---|
| Acceleration                                   | 5 m/s <sup>2</sup>               | Bending cycles                | 12 Mio  |
| Bending cycles at torsion                      | > 5 Mio.                         | Bending radius, min., moving  | 10 x cable diameter   |
| Bending radius, min., stationary               | 5 x cable diameter               | Colour coding                 | brown, white, blue, black   |
| Configurable cable length                      | No                               | Core cross-section            | 0.34 mm <sup>2</sup>  |
| Core in accordance with UL AWM style           | 10493 (80 °C / 300 V)            | Halogen                       | No  |
| Hydrolysis and microbe resistant               | Yes                              | Insulation                    | PP  |
| LABS-free                                      | Yes                              | Length of torsion             | 1 m   |
| Number of poles                                | 4                                | Number of wires               | 4   |
| Outer cladding in accordance with UL AWM style | 20549 (80 °C / 300 V)            | Outside diameter              | 4.7 mm ± 0.2 mm   |
| Resistance to oils                             |                                  | Resistance to spread of flame | in accordance with IEC 60332-1-2, in accordance with IEC 60332-1-3, in accordance with IEC 60332-2-2, In accordance with UL1581 UL/ CUL FT1 |
|  | in accordance with IEC 60811:404 | Sheath material               | PUR   |
| Resistant to welding beads                     | No                               | Shielded                      | No  |
| Sheathing colour                               | black                            | Suitable for cable carriers   | Yes   |
| Speed  | 5 m/s                            | Temperature range, stationary | -40...80 °C   |
| Temperature range, moving                      | -25...80 °C                      | Welding spark resistance      | No  |
| Torsion resistance                             | 360 °/m                          |                               |   |
| Wire cross section (Print/Online)              | 0.34 mm <sup>2</sup>             |                               |   |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001578    | ETIM 7.0    | EC003250    |
| ETIM 8.0    | EC003250    | ETIM 9.0    | EC003250    |
| ECLASS 9.0  | 27-06-20-11 | ECLASS 9.1  | 27-06-90-90 |
| ECLASS 10.0 | 27-06-01-06 | ECLASS 11.0 | 27-06-01-06 |
| ECLASS 12.0 | 27-06-01-06 | ECLASS 13.0 | 27-06-01-06 |

## Approvals

Approvals



ROHS

Conform

## Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a>                               |
| Brochures  | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a> |

**SAIH-4X0,34(PUR)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Cutting tools**

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

**General ordering data**

|            |                            |  |
|------------|----------------------------|--|
| Type       | KT 8                       | Version  |
| Order No.  | <a href="#">9002650000</a> | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163              |  |
| Qty.       | 1 pc(s).                   |  |

**Tools**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

**General ordering data**

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | STRIPPER 6-16 RED-LINE     | Version                    |
| Order No.  | <a href="#">9203110000</a> | Stripping and cutting tool |
| GTIN (EAN) | 4032248541423              |                            |
| Qty.       | 1 pc(s).                   |                            |

## SAIH-4X0,34(PUR)

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Tools

Sheathing stripper for PVC cables



## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | AM 12                      | Version                    |
| Order No.  | <a href="#">9030060000</a> | Tools, Sheathing strippers |
| GTIN (EAN) | 4008190337827              |                            |
| Qty.       | 1 pc(s).                   |                            |

## Screwty® cable gland tool with torque function



## The ideal tool for any application

Screwty® is the ideal, all-purpose tool for tightening all common sensor and actuator cables. Even difficult-to-reach round plugs are accessible using the Screwty®. A simple turning movement tightens and loosens the connectors without the need for excessive force. The Screwty® is a unique and global solution since it fits with most cables and plugs from other vendors (over 90 %). The Screwty® consists of a handle with a conventional 1/4" adapter. Thus it can be used for all sizes: for M12 and M8 round plug-in connectors, and for M12F and M8F customisable plugs and sockets, as well as for all M23 plugs and sockets.

## General ordering data

|            |                            |  |               |
|------------|----------------------------|--|---------------|
| Type       | SCREWTY-M12-DM             | Version                                | Packaging     |
| Order No.  | <a href="#">1900001000</a> | Cable gland tool for moulded M12 lines | Cardboard box |
| GTIN (EAN) | 4032248436408              |  |               |
| Qty.       | 1 pc(s).                   |  |               |
| Type       | SAI-SCREWTY BOX            | Version                                | Packaging     |
| Order No.  | <a href="#">1939180000</a> | Bolting tool                           | Plastic case  |
| GTIN (EAN) | 4032248615506              |  | + form        |
| Qty.       | 1 pc(s).                   |  | insert        |

**SAIH-4X0,34(PUR)****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Blank**

TM-I is an acknowledged and accredited marker type for traffic engineering applications. There are various different tag lengths available for individual labelling with long character strings. Easy handling of separation and installation thanks to the project marker field. Pre-attachment of sleeves and retrofitting of tags offer excellent versatility

The special contour of TM-I allows easy assembly and secures firm positioning. They are compatible with a number of commercially available sleeves. Thanks to the MultiCard format, the tags can be printed quickly and conveniently with the PrintJet CONNECT, plotter or the STI pen.

- Easy handling of separation and installation thanks to the project marker field.
- Acknowledged and accredited marker for traffic engineering applications
- Pre-attachment of sleeves and retrofitting of tags offer excellent versatility
- Not suited for labelling with P-Ink or STI pen in connection with CLI T sleeves

**For custom printing:** Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

**General ordering data**

|            |                            |   |
|------------|----------------------------|---|
| Type       | TM-I 18 MC NE GE           | Version                                 |
| Order No.  | <a href="#">1718431687</a> | TM-I, Insert markers, 18 x 4 mm, yellow |
| GTIN (EAN) | 4008190349028              |   |
| Qty.       | 320 pc(s).                 |   |
| Type       | TM-I 18 MC NE WS           | Version                                 |
| Order No.  | <a href="#">1718431044</a> | TM-I, Insert markers, 18 x 4 mm, white  |
| GTIN (EAN) | 4008190349011              |   |
| Qty.       | 320 pc(s).                 |   |