

**HDC 24D SBU 1M32G****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

**General ordering data**

Version	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Base housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
Order No.	<a href="#">1903220000</a>
Type	HDC 24D SBU 1M32G
GTIN (EAN)	4032248588183
Qty.	1 pc(s).

## HDC 24D SBU 1M32G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	115.7 mm	Depth (inches)	4.555 inch
Height	74 mm	Height (inches)	2.913 inch
Width	55.5 mm	Width (inches)	2.185 inch
Mounting dimension - height	45 mm	Mounting dimension - width	82 mm
Net weight	354 g		

## Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

## Dimensions

Cable entry	w. thread	Height of base B1	5 mm
Height of housing B	74 mm	Hole pitch length A2	82 mm
Total length housing	73 mm	Width base C1	55.5 mm
Width housing C	43 mm		

## General data

EMC housings	No	Housing main material	diecast aluminium
Material of locking element	Stainless steel, rust-proof	Protection degree	IP65 (in plugged condition)
Surface finish	Powder coating		

## Version

BG	4	Cable entry	w. thread
Clamp version	Side-locking clamp	Colour (RAL)	RAL 7035
Design	high	Design of housing	Base housing
Design of locking system	Side-locking clamp on lower side	Internal thread	M 32
Number of cable entry on top	0	Number of cable entry sideways	1
Sealing	NBR	Size	4
Size of cable entries	M 32	Suitable for ModuPlug®	Yes
Top part/bottom part/lid	lower part	Type	Base housing

## Classifications

ETIM 6.0	EC000437	ETIM 7.0	EC000437
ETIM 8.0	EC000437	ETIM 9.0	EC000437
ECLASS 9.0	27-44-02-02	ECLASS 9.1	27-44-02-02
ECLASS 10.0	27-44-02-02	ECLASS 11.0	27-44-02-02
ECLASS 12.0	27-44-02-02	ECLASS 13.0	27-44-02-02

Substance	Acetone
Chemical resistance	Conditionally resistant
Substance	Drilling oil
Chemical resistance	Resistant
Substance	Diesel
Chemical resistance	Resistant
Substance	Ethyl alcohol
Chemical resistance	Resistant

## HDC 24D SBU 1M32G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

Substance	Transmission oil
Chemical resistance	Resistant
Substance	Hydraulic oil
Chemical resistance	Resistant
Substance	Coolant
Chemical resistance	Resistant
Substance	Petroleum benzine
Chemical resistance	Resistant
Substance	Sweat
Chemical resistance	Resistant
Substance	Premium gasoline
Chemical resistance	Conditionally resistant
Substance	Water
Chemical resistance	Resistant
Substance	UV
Chemical resistance	Unstable
Substance	Ozone
Chemical resistance	Unstable

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	e98b2b24-ba23-41bf-8d19-0dda3647412f
Chemical resistance	de.myview.objectmodel.impl.BlockImpl@30bbeeb6 de.myview.objectmodel.impl.BlockImpl@7388075a de.myview.objectmodel.impl.BlockImpl@67ab2cd9 de.myview.objectmodel.impl.BlockImpl@310fa559 de.myview.objectmodel.impl.BlockImpl@5eae2390 de.myview.objectmodel.impl.BlockImpl@6daf5dc8 de.myview.objectmodel.impl.BlockImpl@535c7940 de.myview.objectmodel.impl.BlockImpl@1fb53b1f de.myview.objectmodel.impl.BlockImpl@30a839da de.myview.objectmodel.impl.BlockImpl@27fe631a de.myview.objectmodel.impl.BlockImpl@17d888dc de.myview.objectmodel.impl.BlockImpl@218334fb de.myview.objectmodel.impl.BlockImpl@5094aff8

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Product Change Notification	<a href="#">20220214 Technical change to HDC housings</a> <a href="#">20220214 Technische Änderung bei HDC-Gehäusen</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>

Creation date April 29, 2024 8:50:34 AM CEST

Catalogue status 20.04.2024 / We reserve the right to make technical changes.

## HDC 24D SBU 1M32G

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry at top



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

Type	HDC 10B TOBU 1PG16G	Version
Order No.	<a href="#">1654220000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16
GTIN (EAN)	4008190407049	
Qty.	1 pc(s).	
Type	HDC 24D TOBU 2M20G	Version
Order No.	<a href="#">1336600000</a>	HDC enclosures, Size: 4, Protection degree: IP65, IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 20
GTIN (EAN)	4050118175257	
Qty.	1 pc(s).	
Type	HDC 10B TOBU 1PG21G	Version
Order No.	<a href="#">1654240000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21
GTIN (EAN)	4008190407063	
Qty.	1 pc(s).	
Type	HDC 24D TOBU 1M32G	Version
Order No.	<a href="#">1787290000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248204632	
Qty.	1 pc(s).	
Type	HDC 10B TOBU 1M20G	Version
Order No.	<a href="#">1787600000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20
GTIN (EAN)	4032248204946	
Qty.	1 pc(s).	
Type	HDC 24D TOBU 1PG29G	Version
Order No.	<a href="#">1654320000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29
GTIN (EAN)	4008190407148	
Qty.	1 pc(s).	
Type	HDC 24D TOBU 1M25G	Version
Order No.	<a href="#">1787300000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248204649	
Qty.	1 pc(s).	
Type	HDC 10B TOBU 1M25G	Version
Order No.	<a href="#">1787590000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from top, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248204939	
Qty.	1 pc(s).	

## HDC 24D SBU 1M32G

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Hood, Cable Entry sideways



The special die-cast alloy and the multi-layered surface sealing provide complete protection for the HDC housings.

The cleverly designed interlock system is manufactured from stainless steel. This guarantees a long lifespan with high resistance to corrosion and impact.

The housing interlock system provides integrated safety. Our unique, patented spring system provides the housing interlock with a secure grip and prevents accidental opening.

The laser marking allows for easy and quick identification. Each housing is permanently labelled with a laser marking so that each product can be quickly designated and positioned.

Weidmüller RockStar® IP 65 / NEMA Type 4X housings - your first choice for industrial housings with IP 65 protection.

## General ordering data

Type	HDC 10B TSBU 1PG16G	Version
Order No.	<a href="#">1654070000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 16
GTIN (EAN)	4008190406899	
Qty.	1 pc(s).	
Type	HDC 10B TSBU 1M20G	Version
Order No.	<a href="#">1787560000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 20
GTIN (EAN)	4032248204908	
Qty.	1 pc(s).	
Type	HDC 24D TSBU 1PG29G	Version
Order No.	<a href="#">1654170000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 29
GTIN (EAN)	4008190406998	
Qty.	1 pc(s).	
Type	HDC 24D TSBU 1M25G	Version
Order No.	<a href="#">1787240000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 25
GTIN (EAN)	4032248204588	
Qty.	1 pc(s).	
Type	HDC 10B TSBU 1PG21G	Version
Order No.	<a href="#">1654090000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: PG 21
GTIN (EAN)	4008190406912	
Qty.	1 pc(s).	
Type	HDC 10B TSBU 1M25G	Version
Order No.	<a href="#">1787550000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, Standard, Size of cable entries: M 25
GTIN (EAN)	4032248204892	
Qty.	1 pc(s).	
Type	HDC 24D TSBU 1M32G	Version
Order No.	<a href="#">1787230000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: M 32
GTIN (EAN)	4032248204571	
Qty.	1 pc(s).	
Type	HDC 24D TSBU 1PG21G	Version
Order No.	<a href="#">1654150000</a>	HDC enclosures, Size: 4, Protection degree: IP65 (in plugged condition), Cable entry from side, Plug housing, Side-locking clamp on lower side, high, Size of cable entries: PG 21
GTIN (EAN)	4008190406974	
Qty.	1 pc(s).	