


**ZQV 6/24 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

The plug-in cross-connections feature easy handling and quick installation. This saves a great deal of time during installation in comparison with screwed solutions.

**General ordering data**

Version	Accessories, Cross-connector, 41 A
Order No.	<a href="#">1908990000</a>
Type	ZQV 6/24 GE
GTIN (EAN)	4032248535309
Qty.	10 pc(s).

## ZQV 6/24 GE

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	33.96 mm	Depth (inches)	1.337 inch
Height	192.5 mm	Height (inches)	7.579 inch
Width	3.1 mm	Width (inches)	0.122 inch
Net weight	34.603 g		

## Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-60
Continuous operating temp., max.	130		

## Material data

Material	Wemid	Colour	yellow
UL 94 flammability rating	V-0		

## System specifications

Version	For the terminals
---------	-------------------

## Additional technical data

Installation advice	Direct mounting	Type of fixing	Plugged
---------------------	-----------------	----------------	---------

## Cross-connector

Rated current, 2-pole	41 A	Rated current, multi-pole	41 A
Type	Cross-connector		

## Dimensions

Pitch in mm (P)	8.1 mm
-----------------	--------

## General

Installation advice	Direct mounting	Number of poles	24
---------------------	-----------------	-----------------	----

## Rating data

Rated voltage	400 V	Rated DC voltage	400 V
Rated current	41 A		

## Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

## Important note

Product information	Due to stability and temperature reasons It is only possible to break out 60% of contact elements The usage of cross connectors reduces the rated voltage to 400VThe voltage reduced to 25V if cut cross connection with blank cut edges are used
---------------------	---

**ZQV 6/24 GE****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Approvals**

ROHS	Conform
------	---------

**Downloads**

Approval/Certificate/Document of Conformity	<a href="#">Confirmation of Standards EN 45545-2_2020-10</a>
---	--

Engineering Data	<a href="#">CAD data – STEP</a>
------------------	---------------------------------

Engineering Data	<a href="#">Zuken E3.S</a>
------------------	----------------------------

User Documentation	<a href="#">Operating instructions_ZDU1.5-ZDU35_ZQV.pdf</a> <a href="#">StorageConditionsTerminalBlocks</a> <a href="#">User Manual ZQV 2.5</a>
--------------------	---

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

Brochures	
-----------	--