

**VG M16-1/MS68****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

**General ordering data**

Version	VG MS (standard brass cable gland), Cable glands, straight, M 16, 7 mm, OD min. 5 - OD max. 10 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated
Order No.	<a href="#">1909910000</a>
Type	VG M16-1/MS68
GTIN (EAN)	4032248536832
Qty.	50 pc(s).

## VG M16-1/MS68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	28.5 mm	Height (inches)	1.122 inch
Length	35.5 mm	Length (inches)	1.398 inch
Net weight	26.38 g		

## Temperatures

Operating temperature	-40 °C...100 °C
-----------------------	-----------------

## Certificate numbers cable gland

Approval conditions	DNV, UL, cULus	Certificate no. cable gland (GERML-LOYD)	E-14047
Certificate no. cable gland (UL)	E-199260	Certificate no. cable gland (cULus)	E-199260

## General information

AF size	20 mm	AF size 1	20 mm
AF size 2	20 mm	Cable glands	metric, M 16
Clamp insert	Polyamide	External thread	M 16
Halogen	Yes	Length of thread	7 mm
Material	Brass, nickel-plated	O-Ring	NBR
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Outer cable diameter, max.	10 mm	Outer cable diameter, min.	5 mm
Pitch of thread	1.5 mm	Protection class (UL)	Type 4X
Protection degree	IP54, IP66, IP67, IP68 - 5 bar (30 min.)	Protection degree with GWDR	IP54, IP66, IP67, IP68 - 5 bar (30 min.)
Seal insert	CR	Sealing	NBR
Tightening torque	7 Nm	Torque for cap nut, max.	8.5 Nm
Torque for cap nut, min.	7.5 Nm	Torque for connecting adapter, max.	4.5 Nm
Torque for connecting adapter, min.	3.5 Nm		

## Classifications

ETIM 6.0	EC000441	ETIM 7.0	EC000441
ETIM 8.0	EC000441	ETIM 9.0	EC000441
ECLASS 9.0	27-14-44-32	ECLASS 9.1	27-14-44-32
ECLASS 10.0	27-14-44-32	ECLASS 11.0	27-14-44-32
ECLASS 12.0	27-14-08-01	ECLASS 13.0	27-14-08-01

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	b5ff1f66-ddba-4739-9fc0-0521ddb52139

## Approvals

Approvals



ROHS	Conform
------	---------

### VG M16-1/MS68

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity - Standard brass nickel plated cable gland - DE PS2480 210608 003ISS00</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	

**VG M16-1/MS68****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR M16-NP	Version
Order No.	<a href="#">1736230000</a>	GWDR NP (flat gasket - neoprene), Sealing ring, M 16, Neoprene
GTIN (EAN)	4008190956028	
Qty.	50 pc(s).	

**Vulcanised fibre gasket - KSWF**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	KSWF M16	Version
Order No.	<a href="#">1076680000</a>	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 16, Vulcanized
GTIN (EAN)	4032248838615	fibre
Qty.	25 pc(s).	

**VG M16-1/MS68****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Polyethylene flat gasket - GWDR PO**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	GWDR M16-PO	Version
Order No.	<a href="#">1777930000</a>	GWDR PO (flat gasket - polyethylene), Sealing ring, M 16, Polyethylene
GTIN (EAN)	4032248158195	
Qty.	50 pc(s).	

**Nylon flat gasket - KSWN**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

**General ordering data**

Type	KSWN M16	Version
Order No.	<a href="#">1076630000</a>	KSWN (flat gasket - nylon), Sealing ring, M 16, Nylon 6
GTIN (EAN)	4032248838677	
Qty.	25 pc(s).	

## VG M16-1/MS68

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Brass lock nuts, natural finish



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU M16 MS SC	Version
Order No.	<a href="#">0930640001</a>	SKMU MS (brass locknut), Locknut, M 16, 4 mm, Brass
GTIN (EAN)	4032248976065	
Qty.	50 pc(s).	

## Brass lock nuts, nickel-plated



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

## General ordering data

Type	SKMU M16 MS	Version
Order No.	<a href="#">1736990000</a>	SKMU MS (brass locknut), Locknut, M 16, 2.8 mm, Brass, nickel-plated
GTIN (EAN)	4008190956462	
Qty.	100 pc(s).	