

VG M40-1/MS68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

General ordering data

| | |
|------------|--|
| Version | VG MS (standard brass cable gland), Cable glands, straight, M 40, 9 mm, OD min. 19 - OD max. 28 mm, IP54, IP66, IP67, IP68 - 5 bar (30 min.), Brass, nickel-plated |
| Order No. | 1909940000 |
| Type | VG M40-1/MS68 |
| GTIN (EAN) | 4032248536863 |
| Qty. | 10 pc(s). |

VG M40-1/MS68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Height | 43.5 mm | Height (inches) | 1.713 inch |
| Length | 52.5 mm | Length (inches) | 2.067 inch |
| Net weight | 76.1 g | | |

Temperatures

| | |
|-----------------------|-----------------|
| Operating temperature | -40 °C...100 °C |
|-----------------------|-----------------|

Certificate numbers cable gland

| | | | |
|----------------------------------|----------------|--|----------|
| Approval conditions | DNV, UL, cULus | Certificate no. cable gland (GERML-LOYD) | E-14047 |
| Certificate no. cable gland (UL) | E-199260 | Certificate no. cable gland (cULus) | E-199260 |

General information

| | | | |
|-------------------------------------|--|-------------------------------------|--|
| AF size | 43 mm | AF size 1 | 43 mm |
| AF size 2 | 43 mm | Cable glands | metric, M 40 |
| Clamp insert | Polyamide | External thread | M 40 |
| Halogen | Yes | Length of thread | 9 mm |
| Material | Brass, nickel-plated | O-Ring | NBR |
| Operating temperature range, max. | 100 °C | Operating temperature range, min. | -40 °C |
| Outer cable diameter, max. | 28 mm | Outer cable diameter, min. | 19 mm |
| Pitch of thread | 1.5 mm | Protection class (UL) | Type 4X |
| Protection degree | IP54, IP66, IP67, IP68 - 5 bar (30 min.) | Protection degree with GWDR | IP54, IP66, IP67, IP68 - 5 bar (30 min.) |
| Seal insert | CR | Sealing | NBR |
| Tightening torque | 12 Nm | Torque for cap nut, max. | 18 Nm |
| Torque for cap nut, min. | 16 Nm | Torque for connecting adapter, max. | 12.5 Nm |
| Torque for connecting adapter, min. | 11.5 Nm | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000441 | ETIM 7.0 | EC000441 |
| ETIM 8.0 | EC000441 | ETIM 9.0 | EC000441 |
| ECLASS 9.0 | 27-14-44-32 | ECLASS 9.1 | 27-14-44-32 |
| ECLASS 10.0 | 27-14-44-32 | ECLASS 11.0 | 27-14-44-32 |
| ECLASS 12.0 | 27-14-08-01 | ECLASS 13.0 | 27-14-08-01 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | b5ff1f66-ddba-4739-9fc0-0521ddb52139 |

Approvals

Approvals



| | |
|------|---------|
| ROHS | Conform |
|------|---------|

VG M40-1/MS68

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

| | |
|---|---|
| Approval/Certificate/Document of Conformity | EU Declaration of Conformity - Standard brass nickel plated cable gland - DE PS2480 210608 003ISS00 |
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |
| Brochures | |

VG M40-1/MS68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Neoprene flat gasket - GWDR NP**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | GWDR M40-NP | Version |
| Order No. | 1736270000 | GWDR NP (flat gasket - neoprene), Sealing ring, M 40, Neoprene |
| GTIN (EAN) | 4008190956066 | |
| Qty. | 20 pc(s). | |

Polyethylene flat gasket - GWDR PO

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | GWDR M40-PO | Version |
| Order No. | 1777970000 | GWDR PO (flat gasket - polyethylene), Sealing ring, M 40, Polyethylene |
| GTIN (EAN) | 4032248158232 | |
| Qty. | 50 pc(s). | |

VG M40-1/MS68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Brass lock nuts, natural finish**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|---|
| Type | SKMU M40 MS SC | Version |
| Order No. | 0930640005 | SKMU MS (brass locknut), Locknut, M 40, 4.8 mm, Brass |
| GTIN (EAN) | 4032248976096 | |
| Qty. | 10 pc(s). | |

Brass lock nuts, nickel-plated

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SKMU M40 MS | Version |
| Order No. | 1737030000 | SKMU MS (brass locknut), Locknut, M 40, 5 mm, Brass, nickel-plated |
| GTIN (EAN) | 4008190956509 | |
| Qty. | 50 pc(s). | |