

SAI-AU M12 SB 4THERMO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The trend from IP 20 to IP 67, or rather from machines with cabinets to ones without, reaches its zenith in the IP 67 I/O slaves. In these Plug & Play solutions, the connection of individual conductors is avoided completely. This results in a substantial time-saving and eliminates mistakes in the connection of individual conductors. Today, IP 67 bus modules represent the most modern solution for the connection of sensors and actuators with the best cost-saving potential.

General ordering data

Version	SAI Active, Subbus
Order No.	1938720000
Type	SAI-AU M12 SB 4THERMO
GTIN (EAN)	4032248612703
Qty.	1 pc(s).

SAI-AU M12 SB 4THERMO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	32 mm	Height (inches)	1.26 inch
Width	30 mm	Width (inches)	1.181 inch
Length	155 mm	Length (inches)	6.102 inch
Net weight	282 g		

Temperatures

Storage temperature	-25 °C...85 °C	Operating temperature	0 °C...60
---------------------	----------------	-----------------------	-----------

Connections

Connection to Subbus (SUB-IN)	1 x M8 plug 4-pole, A-coded	Connection to Subbus (SUB-OUT)	1 x M8 female 4-pole, A-coded
I/O connections	4 x M12 female, 5-pole A-coded		

Digital inputs

Diagnosis indication	red	Input filter	configurable
----------------------	-----	--------------	--------------

Digital outputs

Diagnosis indication	red
----------------------	-----

General data

Certificate	CE, cULus	Earth	< 200 g
Housing main material	Pocan, PBT	Protection degree	IP67
UL 94 flammability rating	5VA		

Supply voltage

Limits	18 V DC ... 30 V DC	Operating voltage	24 V
Reverse polarity protection	Yes		

Classifications

ETIM 6.0	EC001601	ETIM 7.0	EC001601
ETIM 8.0	EC001601	ETIM 9.0	EC001601
ECLASS 9.0	27-24-26-05	ECLASS 9.1	27-24-26-90
ECLASS 10.0	27-24-26-05	ECLASS 11.0	27-24-26-05
ECLASS 12.0	27-24-26-05	ECLASS 13.0	27-24-26-05

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	30ca4bfe-b33c-43ed-b218-3746bc09f6a6

SAI-AU M12 SB 4THERMO

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads

Approval/Certificate/Document of Conformity	Declaration of Conformity DE PN45 CE Declaration of Conformity - DE UKCA Declaration of Conformity - EN
Engineering Data	CAD data – STEP
User Documentation	MAN UR67 SAI-Aktive Universal Pro DE MAN UR67 SAI-Aktive Universal Pro EN
Catalogues	Catalogues in PDF-format
Brochures	

SAI-AU M12 SB 4THERMO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold


Germany

www.weidmueller.com**Accessories****M12**

Protective caps protect unassigned plug-in stations against external influences.

General ordering data

Type	SAI-SK-M12-UNI 2029	Version
Order No.	2330260000	Protected component assemblies, Protective cap
GTIN (EAN)	4032248592067	
Qty.	20 pc(s).	

Blank

ESG is the tried-and-tested marker in MultiCard format for use on many well-known electrical devices. The result is high-quality device marking with a high-contrast appearance.

Various types are available for devices from manufacturers like Siemens, ABB, Beckhoff etc.

Advantages at a glance:

- Tags for universal usage, self-adhesive or clip-on tags, depending on type
- For aligned equipment, e.g. circuit breakers, we supply ESG markers for clipping onto tag rails
- Individual laser-quality printing according to specifications

For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

General ordering data

Type	ESG 8/13.5/43.3 SAI AU	Version
Order No.	1912130000	ESG, Device markers x 13.5 mm, PA 66, Colour: Transparent
GTIN (EAN)	4032248541164	
Qty.	5 pc(s).	

SAI-AU M12 SB 4THERMO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****M8**

Protective caps protect unassigned plug-in stations against external influences.

General ordering data

Type	SAI-SK M8	Version
Order No.	1802760000	Protected component assemblies, Protective cap
GTIN (EAN)	4032248257379	
Qty.	50 pc(s).	