

BFEL + BEMU WEW WTL 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Screws for fixing the cover profiles complete the contact protection.

General ordering data

Version	W-Series, Fastening element
Order No.	1964820000
Type	BFEL + BEMU WEW WTL 35
GTIN (EAN)	4032248651467
Qty.	20 pc(s).

BFEL + BEMU WEW WTL 35**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	8 mm	Depth (inches)	0.315 inch
Height	14.5 mm	Height (inches)	0.571 inch
Width	14.5 mm	Width (inches)	0.571 inch
Diameter	14.5 mm	Net weight	1.3 g

Temperatures

Storage temperature	-25 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	120 °C		

Material data

Material	Wemid	Colour	dark beige
UL 94 flammability rating	V-0		

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Dimensions

Diameter	14.5 mm
----------	---------

General

Installation advice	Direct mounting
---------------------	-----------------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ETIM 9.0	EC002848
ECLASS 9.0	27-14-11-92	ECLASS 9.1	27-14-11-92
ECLASS 10.0	27-14-11-92	ECLASS 11.0	27-14-11-92
ECLASS 12.0	27-14-11-92	ECLASS 13.0	27-25-03-90

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format