

IE-BP-V05M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For protecting your devices against dust and dirt.

General ordering data

Version	Flange-mounted housing, protective cap
Order No.	1968930000
Type	IE-BP-V05M
GTIN (EAN)	4032248692125
Qty.	10 pc(s).

IE-BP-V05M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Depth	17.5 mm	Depth (inches)	0.689 inch
Net weight	11.778 g		

Temperatures

Operating temperature	-40 °C...70
-----------------------	-------------

General data

Colour	grey	Housing main material	diecast aluminium
Protection degree	IP67		

Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ETIM 9.0	EC002314
ECLASS 9.0	27-44-02-08	ECLASS 9.1	27-44-02-08
ECLASS 10.0	27-44-02-08	ECLASS 11.0	27-44-02-08
ECLASS 12.0	27-44-02-08	ECLASS 13.0	27-44-02-08

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	4f3aae94-c2bc-4010-b63b-5b114ba6bd55

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN FL FIELDWIRING EN PI PROFINET CABLING EN