

**SCREWTY M23****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The Screwty® attachment is suitable for customisable M23 round plug-in connectors and for overmoulded M23 round plug-in connectors, with an outside dimension of the knurled nut of  $26.2 \pm 0.3$  mm. The tightening torque is 2-2.5 Nm.

**General ordering data**

Version	Cable gland tool adapter for M23 lines and connectors
Order No.	<a href="#">1981560000</a>
Type	SCREWTY M23
GTIN (EAN)	4032248677702
Qty.	1 pc(s).
Packaging	Plastic bag

**SCREWTY M23****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Net weight	23 g
------------	------

**Screwing tools**

Connection thread	M23	Size	26.2 mm
-------------------	-----	------	---------

**Classifications**

ETIM 6.0	EC000149	ETIM 7.0	EC000149
ETIM 8.0	EC000149	ETIM 9.0	EC000149
ECLASS 9.0	21-04-50-03	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-50-03	ECLASS 11.0	21-01-90-90
ECLASS 12.0	21-01-90-90	ECLASS 13.0	21-01-90-90

**Downloads**

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">FL FIELDWIRING EN</a>