

FAD BLK7 2XHE20 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Order No.	1985960000
Type	FAD BLK7 2XHE20 M
GTIN (EAN)	4050118371000
Qty.	1 pc(s).

FAD BLK7 2XHE20 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	36 mm	Depth (inches)	1.417 inch
Height	218 mm	Height (inches)	8.583 inch
Width	54 mm	Width (inches)	2.126 inch
Net weight	210 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50
---------------------	-------------	-----------------------	----------

Connection data

Connection (field side)	2 x Connector according IEC60603-13/DIN41651 20 p
-------------------------	---

Ratings data

Operating voltage	30 V AC / 60 V DC	Max. current per channel	1 A
Max. current per byte	2 A	Total operating current	6 A

Insulation coordination (EN50178)

According to	DIN EN 50178	Rated insulation voltage	< 250 V AC
Surge voltage category	III	Pollution severity level	2
Insulation test voltage AC	1.2 kV	Storage temperature, min.	-40 °C
Storage temperature, max.	60 °C		

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ETIM 9.0	EC002780
ECLASS 9.0	27-14-11-52	ECLASS 9.1	27-24-22-16
ECLASS 10.0	27-14-11-52	ECLASS 11.0	27-14-11-52
ECLASS 12.0	27-14-11-52	ECLASS 13.0	27-14-11-52

Approvals

Approvals



ROHS

Conform

Downloads

Approval/Certificate/Document of Conformity

[Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

FAD BLK7 2XHE20 M

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings