

HDC FLDG 10B IP68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

We offer a variety of accessories, including seals, to accompany the housings.

Because of the excellent sealing, you can achieve the best seal possible with our housings.

Extensive testing has confirmed it – RockStar® remains impermeable to water to a depth of 50 metres. This allows you to use heavy-duty connectors in environments which previously required fixed-wire installation.

General ordering data

Version	Accessories, Enclosures accessories, Protection degree: Design of housing: Clamp version: Design: Approvals :
Order No.	1987500000
Type	HDC FLDG 10B IP68
GTIN (EAN)	4050118379211
Qty.	1 pc(s).

HDC FLDG 10B IP68**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	3 g
------------	-----

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

Version

BG	4	Colour (RAL)	RAL 3020
Sealing	Silicone	Size	4

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-01-92
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	61018_HDC_FLDG_10B_IP68_CUSTOMER_DRAWING_C
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN