

SAI-M23-BE-L-4/4**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The M23 round plug-in connectors offer a high number of mating cycles, high current-carrying capacity and high contact-density coupled with minimum dimensions. Enclosures, inserts and crimp contacts need to be ordered separately.

General ordering data

Version	Sensor/Actuator plug-in connector, Insert
Order No.	1995810000
Type	SAI-M23-BE-L-4/4
GTIN (EAN)	4032248925674
Qty.	1 pc(s).

SAI-M23-BE-L-4/4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	10 g
------------	------

Technical data customisable plug-in connectors

Coding	none	Housing main material	Thermoplastic polyamide PA 6, PBT
Number of poles	8	Plugging cycles	> 1000
Pollution severity	3	Rated current	1 mm contact = 8 A, 2 mm contact= 28 A
Type of connection	Crimp connection		

Classifications

ETIM 6.0	EC000438	ETIM 7.0	EC003557
ETIM 8.0	EC003557	ETIM 9.0	EC003557
ECLASS 9.1	27-44-02-05	ECLASS 10.0	27-44-02-23
ECLASS 11.0	27-44-02-23	ECLASS 12.0	27-44-02-23
ECLASS 13.0	27-44-02-23		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E344862

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN

SAI-M23-BE-L-4/4

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26


D-32758 Detmold

Germany


www.weidmueller.com

Drawings

Pinning



Dimensioned drawing



Technical data

		5 + PE		4/4	
No. of poles		5 + PE		4/4	
Number of contacts		6		4	4
Contact-ø	mm	2	1	2	

4 times 1-mm female and 4 times 2-mm female