

CC 15/60 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Standard included: CC**

Our systematically matching product range includes labels for identifying standardised components, as well as all-purpose and familiar formats such as the CC 85/54 marker for nameplates.

Your benefits with MultiMark

- “Different materials for various requirements”
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|--------------------|---|
| Version | ClipCard, Device markers, 15 x 60 mm, white |
| Order No. | 2005410000 |
| Type | CC 15/60 MM WS |
| GTIN (EAN) | 4050118391077 |
| Qty. | 450 pc(s). |
| compatible printer | 2599430000 2599440000 |

CC 15/60 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|--------|-----------------|------------|
| Depth | 0.1 mm | Depth (inches) | 0.004 inch |
| Height | 15 mm | Height (inches) | 0.591 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Net weight | 0.31 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -40...120 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|-----------------------------|-----------------------------------|--------|
| Adhesive | Acrylate adhesive | Approval acc. to UL 969 | Yes |
| Colour | white | Halogen | No |
| Material | Polyester | Number per roll | 450 |
| Operating temperature range | -40...120 °C | Operating temperature range, max. | 120 °C |
| Operating temperature range, min. | -40 °C | UL 94 flammability rating | V-0 |
| Version | Self-adhesive, halogen-free | Width | 60 mm |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ETIM 9.0 | EC001288 |
| ECLASS 9.0 | 27-40-06-29 | ECLASS 9.1 | 27-40-06-29 |
| ECLASS 10.0 | 27-40-06-29 | ECLASS 11.0 | 27-28-11-04 |
| ECLASS 12.0 | 27-28-11-04 | ECLASS 13.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |

CC 15/60 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

