

TST 10 SAKC10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

In contrast to the terminal blocks with integrated disconnect lever, our disconnect plugs can be completely detached or removed from the terminal block and the respective application and offer a flexible alternative solution to our standard disconnectors.

General ordering data

Version	Mounting foot for mounting rail, Polyamide 66
Order No.	2082460000
Type	TST 10 SAKC10
GTIN (EAN)	4008190223380
Qty.	400 pc(s).

TST 10 SAKC10

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	7.4 mm	Depth (inches)	0.291 inch
Height	51 mm	Height (inches)	2.008 inch
Width	7.4 mm	Width (inches)	0.291 inch
Net weight	3.578 g		

Temperatures

Continuous operating temp., min.	-50 °C	Continuous operating temp., max.	100 °C
----------------------------------	--------	----------------------------------	--------

Material data

Material	Polyamide 66	Colour	red
UL 94 flammability rating	V-2		

System specifications

Version	For the mounting rails
---------	------------------------

General

Operating temperature range, max.	100 °C
-----------------------------------	--------

Classifications

ETIM 6.0	EC002625	ETIM 7.0	EC002625
ETIM 8.0	EC002625	ETIM 9.0	EC002625
ECLASS 9.0	27-18-28-07	ECLASS 9.1	23-15-90-90
ECLASS 10.0	27-18-28-07	ECLASS 11.0	27-18-28-07
ECLASS 12.0	27-18-28-07	ECLASS 13.0	27-18-28-07

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	45173c19-8a33-4947-bc2b-512a20c76dcd

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--