

SAKQB 6/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Cross-connector (terminal), when screwed in, Number of poles: 10, Pitch in mm (P): 8.00, Insu- lated: No
Order No.	2111230000
Type	SAKQB 6/10
GTIN (EAN)	4050118440607
Qty.	10 pc(s).
Local product	Only available in certain countries

SAKQB 6/10**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****General ordering data**

Local product	Only available in certain countries
---------------	-------------------------------------

Dimensions and weights

Depth	15 mm	Depth (inches)	0.591 inch
Width	6 mm	Width (inches)	0.236 inch
Net weight	19.74 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Additional technical data

Type of fixing	when screwed in
----------------	-----------------

Dimensions

Pitch in mm (P)	8 mm
-----------------	------

General

Number of poles	10
-----------------	----

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format