

FAD S5135 SL42 A R**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The front adapters for migration are connected to the old PLC and, by means of a new pre-assembled cable, to the new one. Some adapters have 2 connectors for redundancy.

General ordering data

Version	
Order No.	2435110000
Type	FAD S5135 SL42 A R
GTIN (EAN)	4050118446975
Qty.	1 pc(s).

FAD S5135 SL42 A R

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	23 mm	Depth (inches)	0.906 inch
Height	283 mm	Height (inches)	11.142 inch
Width	20 mm	Width (inches)	0.787 inch
Net weight	127 g		

Temperatures

Storage temperature	-40...60 °C	Operating temperature	-25...50 °C
---------------------	-------------	-----------------------	-------------

Connection data

Connection (field side)	SL 5.08 mm
-------------------------	------------

Ratings data

Operating voltage	250 V AC	Max. current per channel	4 A
Total operating current	32 A		

Insulation coordination (EN50178)

Rated insulation voltage	< 250 V AC	Surge voltage category	II
Pollution severity level	2	Insulation test voltage AC	1.2 kV

Classifications

ETIM 6.0	EC002584	ETIM 7.0	EC002584
ETIM 8.0	EC002584	ETIM 9.0	EC002584
ECLASS 9.0	27-33-02-92	ECLASS 9.1	27-24-22-92
ECLASS 10.0	27-33-02-92	ECLASS 11.0	27-33-02-92
ECLASS 12.0	27-33-02-92	ECLASS 13.0	27-33-02-92

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	9d5ff7ee-74dc-449b-a1db-a29604b9b3e9

Approvals

Approvals



ROHS

Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FAD S5135 SL42 A R

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

