

SAIB-VSA-3P/24/9/SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly. Customisable valve plugs are used frequently in special-purpose machine engineering. Such plugs are used to connect solenoid valves. The valve plugs are available in all standard design types. The range includes the design types A, B Industrial, B acc. to DIN, C Industrial and C acc. to DIN. The valve plugs are available in 3 and 4-pole versions without cables. A flat gasket seal is included which, when screwed on, guarantees IP 65 protection.

General ordering data

Version	Field attachable connector, Valve plug, Socket, angled
Order No.	2451220000
Type	SAIB-VSA-3P/24/9/SD
GTIN (EAN)	4050118465426
Qty.	1 pc(s).

SAIB-VSA-3P/24/9/SD

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 26 g

Technical data customisable plug-in connectors

All valve plugs are fitted with protective circuits	Suppressor diode	Cable diameter, max.	7 mm
Cable diameter, min.	4.5 mm	Coding	Design A (18 mm)
Connection cross-section, max.	1.5 mm ²	Contact surface	CuSn
Housing main material	PA 6 GF	LED	No
Number of poles	3	Plugging cycles	≤ 50
Pollution severity	3	Protection degree	IP65
Rated current	10 A	Rated voltage	24 V
Shield connection	No	Temperature range of housing	-30...+90 °C
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002062	ETIM 7.0	EC003623
ETIM 8.0	EC003623	ETIM 9.0	EC003623
ECLASS 9.0	27-44-01-05	ECLASS 9.1	27-44-01-05
ECLASS 10.0	27-44-01-05	ECLASS 11.0	27-44-01-05
ECLASS 12.0	27-44-01-05	ECLASS 13.0	27-44-01-05

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)
 Brochures [FL FIELDWIRING EN](#)