

EPG CUT 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Weidmüller is a specialist in the cutting of copper or aluminium cables. The range of products extends from cutting tools with direct force application for small cross-sections up to cutting tools for large diameters.

- Extremely fast processing thanks to two-stage hydraulic pump
- 360° revolving quick action crimping head
- Ergonomic handle and balanced weight distribution ensure fatigue-free and safe operation
- Permanent battery charge level control
- Monitoring of the working cycle and status display
- Error display in the event of malfunctions

General ordering data

Version	Cutting tools, Cutting tool
Order No.	2453830000
Type	EPG CUT 40
GTIN (EAN)	4050118468410
Qty.	1 pc(s).

EPG CUT 40

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	70 mm	Depth (inches)	2.756 inch
Height	365 mm	Height (inches)	14.37 inch
Width	80 mm	Width (inches)	3.15 inch
Net weight	3,100 g		

Technical data

Charging time	0.5 h	Operating voltage	18 V DC
---------------	-------	-------------------	---------

Cutting tools

Charging time	0.5 h	Copper cable - solid, max.	240 mm ²
Copper cable - stranded, max.	200 mm ²	Copper cable, max. diameter	40 mm
Operating voltage	18 V DC	Punching force	30 kN
Single-core aluminium cable, max.(mm ²)	500 mm ²	Stranded aluminium cable, max (mm ²)	280 mm ²
Stranded aluminium cable, max. diameter	40 mm		

Classifications

ETIM 6.0	EC000142	ETIM 7.0	EC000142
ETIM 8.0	EC000142	ETIM 9.0	EC000142
ECLASS 9.0	21-04-47-01	ECLASS 9.1	21-04-37-06
ECLASS 10.0	21-04-47-01	ECLASS 11.0	21-04-47-01
ECLASS 12.0	21-04-47-01	ECLASS 13.0	21-04-47-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

EPG CUT 40

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Example of use



EPG CUT 40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Accessories****Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

General ordering data

Type	AKKU APG/EPG 5AH
Order No.	2860070000
GTIN (EAN)	4064675574750
Qty.	1 pc(s).
Type	LADEGERAET EPG
Order No.	1509370000
GTIN (EAN)	4050118318630
Qty.	1 pc(s).
Type	AKKU APG/EPG 2AH
Order No.	2858730000
GTIN (EAN)	4064675566137
Qty.	1 pc(s).