

**ES EPG/HPG 60 WM 240****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Similar to illustration****Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

**General ordering data**

Version	Crimping tool insert, WM crimp
Order No.	<a href="#">2469640000</a>
Type	ES EPG/HPG 60 WM 240
GTIN (EAN)	4050118484052
Qty.	1 pc(s).

## ES EPG/HPG 60 WM 240

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	22 mm	Depth (inches)	0.866 inch
Height	42 mm	Height (inches)	1.654 inch
Width	42 mm	Width (inches)	1.654 inch
Net weight	117 g		

### Crimp inserts

Crimp cross-section copper	240	Crimping width	5 mm
Crimping width in mm	5		

### Description of contact

Conductor cross-section, max. AWG	450	Type of contact	Euro series cable lug
-----------------------------------	-----	-----------------	-----------------------

### tool data crimping

Cable lug cross section	nominal	240 mm <sup>2</sup>
Crimping type/profile	WM crimp	

### Classifications

ETIM 6.0	EC001282	ETIM 7.0	EC001282
ETIM 8.0	EC001282	ETIM 9.0	EC001282
ECLASS 9.0	21-04-90-90	ECLASS 9.1	21-01-90-90
ECLASS 10.0	21-04-90-90	ECLASS 11.0	21-04-90-90
ECLASS 12.0	21-04-90-90	ECLASS 13.0	21-04-90-90

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

## ES EPG/HPG 60 WM 240

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### Tools



#### Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 400 mm<sup>2</sup>
- 360° revolving quick action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- Additional features for APG series:
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB

#### General ordering data

Type	HPG 60	Version
Order No.	<a href="#">2453820000</a>	6mm <sup>2</sup> , 300mm <sup>2</sup> , Hexagonal crimp, WM crimp, Indent crimp,
GTIN (EAN)	4050118468427	Trapezoidal crimp, Oval crimping
Qty.	1 pc(s).	

### 240 mm<sup>2</sup>



#### The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

#### General ordering data

Type	VSTN/-240	Version
Order No.	<a href="#">1497400000</a>	cable lug, terminal end, 240 mm <sup>2</sup> , 240 mm <sup>2</sup>
GTIN (EAN)	4050118306965	
Qty.	25 pc(s).	

**ES EPG/HPG 60 WM 240****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****240 mm<sup>2</sup>**

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

**General ordering data**

Type	KWN-M10/-240 90	Version
Order No.	<a href="#">1494590000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304145	
Qty.	25 pc(s).	
Type	KWN-M12/-240 90	Version
Order No.	<a href="#">1494610000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304244	
Qty.	25 pc(s).	
Type	KWN-M16/-240 90	Version
Order No.	<a href="#">1494620000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304237	
Qty.	25 pc(s).	
Type	KWN-M20/-240 90	Version
Order No.	<a href="#">1494630000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304138	
Qty.	25 pc(s).	

## ES EPG/HPG 60 WM 240

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Tools


**Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts**

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm<sup>2</sup>
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 1.5 Ah

## General ordering data

Type	EPG 60	Version
Order No.	<a href="#">2453810000</a>	Pressing tools, Tools, Pressing tool, 6mm <sup>2</sup> , 300mm <sup>2</sup> , Hexagonal crimp,
GTIN (EAN)	4050118468434	WM crimp, Indent crimp, Trapezoidal crimp, Oval crimping
Qty.	1 pc(s).	

240 mm<sup>2</sup>
**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M16/-240 S	Version
Order No.	<a href="#">1494370000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304046	
Qty.	5 pc(s).	
Type	KRN-M10/-240 S	Version
Order No.	<a href="#">1494340000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304039	
Qty.	5 pc(s).	
Type	KRN-M12/-240 S	Version
Order No.	<a href="#">1494350000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118303933	
Qty.	5 pc(s).	

## ES EPG/HPG 60 WM 240

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

240 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KWN-M12/-240 45	Version
Order No.	<a href="#">1495400000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305227	
Qty.	15 pc(s).	
Type	KWN-M20/-240 45	Version
Order No.	<a href="#">1495420000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305234	
Qty.	15 pc(s).	
Type	KWN-M16/-240 45	Version
Order No.	<a href="#">1495410000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305203	
Qty.	15 pc(s).	

240 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KP-M10/-240	Version
Order No.	<a href="#">1498390000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118307818	
Qty.	20 pc(s).	
Type	KP-M16/-240	Version
Order No.	<a href="#">1498420000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118307825	
Qty.	20 pc(s).	

## ES EPG/HPG 60 WM 240

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

Type	KP-M12/-240	Version
Order No.	<a href="#">1498410000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118307672	
Qty.	20 pc(s).	
Type	KP-M20/-240	Version
Order No.	<a href="#">1498430000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118307832	
Qty.	20 pc(s).	
Type	KP-M14/-240	Version
Order No.	<a href="#">1498530000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118307689	
Qty.	20 pc(s).	

240 mm<sup>2</sup>

**The use of insulated connectors guarantees users consistent electrical connection quality in the long term.**

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

## General ordering data

Type	KRN-M10/-240	Version
Order No.	<a href="#">1495490000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305050	
Qty.	25 pc(s).	
Type	KRN-M16/-240	Version
Order No.	<a href="#">1495510000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304770	
Qty.	25 pc(s).	
Type	KRN-M20/-240	Version
Order No.	<a href="#">1495520000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305104	
Qty.	25 pc(s).	
Type	KRN-M8/-240	Version
Order No.	<a href="#">1495480000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118304756	
Qty.	25 pc(s).	
Type	KRN-M14/-240	Version
Order No.	<a href="#">1497270000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118306842	
Qty.	25 pc(s).	
Type	KRN-M12/-240	Version
Order No.	<a href="#">1495500000</a>	cable lug, terminal end, 240 mm <sup>2</sup>
GTIN (EAN)	4050118305142	
Qty.	25 pc(s).	