

**FP ESWB TERMINAL SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The combination of FieldPower® Elevator and flat cable allows to integrate different functionalities per hoistway landing into one solution: safety chain, bus communication and power distribution. No special tool is required for a quick and easy installation.

**General ordering data**

Version	Wiring box for elevator shaft
Order No.	<a href="#">2524850000</a>
Type	FP ESWB TERMINAL SET
GTIN (EAN)	4050118536430
Qty.	1 pc(s).
Packaging	Box

**FP ESWB TERMINAL SET****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	64.5 mm	Depth (inches)	2.539 inch
Height	122 mm	Height (inches)	4.803 inch
Width	96 mm	Width (inches)	3.78 inch
Net weight	261.28 g		

**Temperatures**

Storage temperature	-5 °C...50 °C	Operating temperature	-5 °C...50 °C
---------------------	---------------	-----------------------	---------------

**Classifications**

ETIM 6.0	EC000214	ETIM 7.0	EC000214
ETIM 8.0	EC000214	ETIM 9.0	EC000214
ECLASS 9.0	27-14-24-09	ECLASS 9.1	27-14-24-09
ECLASS 10.0	27-14-24-09	ECLASS 11.0	27-14-24-09
ECLASS 12.0	27-14-24-09	ECLASS 13.0	27-14-24-09

**Environmental Product Compliance**

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	5f19cd84-8946-4797-9386-3ac323b95c10

**Important note**

Product information	The elevator shaft wiring box can be used with approved flat cable from manufacturer Draka EHC.
---------------------	---

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Installation Instructions FieldPower® Elevator Shaft Wiring Box</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## FP ESWB TERMINAL SET

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

