


HS-HF 6.4-12.7/12 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

General ordering data

| | |
|--------------------|--|
| Version | Conductor and cable markers, 6.4 - 12.7 mm, 12.7 x 20.9 mm, yellow |
| Order No. | 2526340000 |
| Type | HS-HF 6.4-12.7/12 MM Y |
| GTIN (EAN) | 4050118537499 |
| Qty. | 2,000 pc(s). |
| compatible printer | 2599430000 2599440000 |

HS-HF 6.4-12.7/12 MM Y

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.77 mm | Depth (inches) | 0.03 inch |
| Height | 12.7 mm | Height (inches) | 0.5 inch |
| Width | 20.9 mm | Width (inches) | 0.823 inch |
| Net weight | 0.467 g | | |

Temperatures

| | |
|-----------------------------|--------------|
| Operating temperature range | -55...105 °C |
|-----------------------------|--------------|

General data

| | | | |
|-----------------------------------|--------------|-----------------------------------|---------|
| Colour | yellow | Halogen | No |
| Material | Polyolefine | Number per roll | 2,000 |
| Operating temperature range | -55...105 °C | Operating temperature range, max. | 105 °C |
| Operating temperature range, min. | -55 °C | Width | 20.9 mm |

Conductor and cable markers

| | | | |
|-----------------------------------|-------------------|----------------------------------|------------------------|
| Conductor O.D. | 6.4 - 12.7 mm | Conductor O.D., max. | 12.7 mm |
| Conductor O.D., min. | 6.4 mm | Conductor cross-section, max. | 35 mm ² |
| Conductor cross-section, min. | 6 mm ² | Cross-section for connected wire | 6 - 35 mm ² |
| Halogen | No | Rate of shrinkage | 2:1 |
| Recommended shrinking temperature | 90 °C | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001530 | ETIM 7.0 | EC001530 |
| ETIM 8.0 | EC001530 | ETIM 9.0 | EC001530 |
| ECLASS 9.0 | 27-40-04-01 | ECLASS 9.1 | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | NFX 70-100-1 2006 + NF X 70-100-2 2006 BS EN ISO 4589-2 1999 EN 45545-2:2020 |
| Catalogues | Catalogues in PDF-format |

HS-HF 6.4-12.7/12 MM Y

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



HS-HF 6.4-12.7/12 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | THM MMP ROLLER 115 |
| Order No. | 1357420000 |
| GTIN (EAN) | 4050118160314 |
| Qty. | 1 pc(s). |

Ink ribbons

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data


| | | |
|------------|----------------------------|------------|
| Type | RIBBON MM-HS 60/300 SW | Version |
| Order No. | 2448880000 | Ink ribbon |
| GTIN (EAN) | 4050118462944 | |
| Qty. | 1 pc(s). | |

HS-HF 6.4-12.7/12 MM Y**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****THM MULTIMARK PLUS**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

General ordering data

| | |
|------------|----------------------------|
| Type | MM PLUS ROLLER 110 |
| Order No. | 2672590000 |
| GTIN (EAN) | 4050118708097 |
| Qty. | 1 pc(s). |