

**DG M20 PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Intelligent cabling solutions can save you valuable time and money.**

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread  
Integration of operating and signalling devices into the seal possible

**General ordering data**

Version	Field Power® sealing insert, Seal with connection thread, IP65, with corresponding enclosure, EPDM
Order No.	<a href="#">2545550000</a>
Type	DG M20 PT6
GTIN (EAN)	4050118555530
Qty.	1 pc(s).

## DG M20 PT6

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	19.5 mm	Depth (inches)	0.768 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Net weight	21.558 g		

## Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
---------------------	----------------	-----------------------	----------------

## General data

Material	EPDM	Silicone	No
Colour	black	Design	Seal with connection thread
Protection degree	IP65, with corresponding enclosure	UL 94 flammability rating	HB
Mounting position, installation notice	in FieldPower® sealing slot	Internal thread	M 20
Version	Threaded adapter M20		

## Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ETIM 9.0	EC002624
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-28-15
ECLASS 11.0	27-18-28-15	ECLASS 12.0	27-18-28-15
ECLASS 13.0	27-18-28-15		

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E256877

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration FieldPower® Enclosure parts</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**DG M20 PT6****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories****Socket**

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Type	SAIE-7/8-B-5-0.2U-M20	Version
Order No.	<a href="#">1398710000</a>	Built-in plugs, 7/8", Mounting thread: M 20, Number of poles: 5,
GTIN (EAN)	4050118200607	Strand / cable length: 0.2 m
Qty.	1 pc(s).	

**Pin**

Various build-in connectors are required for the connections on the device side of the sensor/actuator cabling. These are available in the versions M12, M8 and M5.

**General ordering data**

Type	SAIE-7/8-S-5-0.2U-M20	Version
Order No.	<a href="#">1471490000</a>	Built-in plugs, 7/8", Mounting thread: M 20, Number of poles: 5,
GTIN (EAN)	4050118278729	Strand / cable length: 0.2 m
Qty.	1 pc(s).	

## DG M20 PT6

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## IP68 version



In addition to the extensive range of enclosures, Weidmüller offers a variety of cable glands for a wide range of applications.

The cable glands made of brass, plastic and stainless steel meet the most various IP protection classes to suit any industrial enclosure.

Depending on the series of cable glands and the application, the cable glands are approved and tested according to VDE, UL, UR, cULus, DNV GL or EN 45545.

## General ordering data

Type	VG M20 - K 68	Version
Order No.	<a href="#">2811470000</a>	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10
GTIN (EAN)	4064675292227	mm, OD min. 10 - OD max. 14 mm, IP54, IP66, IP67, IP68 - 5 bar (30
Qty.	50 pc(s).	min.), Polyamide 6
Type	VG M20-1/K68	Version
Order No.	<a href="#">1772300000</a>	VG K (standard plastic cable gland), Cable glands, straight, M 20, 10
GTIN (EAN)	4032248129966	mm, OD min. 6 - OD max. 12 mm, IP54, IP66, IP67, IP68 - 5 bar (30
Qty.	50 pc(s).	min.), Polyamide 6

## IE fastening tool



The mounting tool helps you to tighten the locknut when mounting the flange of version 04.

**Comments:**

- Standard tool
- made from tough plastic

## General ordering data

Type	IE-FISP-V4	Version
Order No.	<a href="#">9204370000</a>	Mounting tool
GTIN (EAN)	4032248660780	
Qty.	2 pc(s).	