

**CD-SE 40/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Version	Cable duct separator, 40 mm x
Order No.	<a href="#">2553950000</a>
Type	CD-SE 40/2
GTIN (EAN)	4050118564082
Qty.	30 pc(s).

**CD-SE 40/2****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	40 mm	Height (inches)	1.575 inch
Length	1,000 mm	Length (inches)	39.37 inch
Net weight	210 g		

**Temperatures**

Operating temperature range	-5...60 °C
-----------------------------	------------

**General information**

Colour	grey	Material	PVC
Non-tracking	Yes	Operating temperature range	-5...60 °C
UL 94 flammability rating	V-0	Version	2-walled

**Classifications**

ETIM 6.0	EC001015	ETIM 7.0	EC001015
ETIM 8.0	EC001015	ETIM 9.0	EC001015
ECLASS 9.1	27-40-07-52	ECLASS 10.0	27-40-07-52
ECLASS 11.0	27-40-07-52	ECLASS 12.0	27-40-07-52
ECLASS 13.0	27-40-07-52		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--