

**FF-FIMT 11 54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

**General ordering data**

Version	Filter mat, IP54, white
Order No.	<a href="#">2556600000</a>
Type	FF-FIMT 11 54
GTIN (EAN)	4050118567229
Qty.	5 pc(s).

**FF-FIMT 11 54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	87 mm	Height (inches)	3.425 inch
Width	87 mm	Width (inches)	3.425 inch
Net weight	3.2 g		

**Temperatures**

Operating temperature range	-40...55 °C
-----------------------------	-------------

**General data**

Colour	white	Filter class	G 4
Operating temperature range	-40...55 °C	Protection class (UL)	Type 12
Type of mounting	Snap-on	With filter	Yes

**Classifications**

ETIM 6.0	EC002513	ETIM 7.0	EC002513
ETIM 8.0	EC002513	ETIM 9.0	EC002513
ECLASS 9.1	27-18-07-06	ECLASS 10.0	27-18-07-06
ECLASS 11.0	27-18-07-06	ECLASS 12.0	27-18-07-06
ECLASS 13.0	27-18-07-06		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Operating instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>