


**FF 66 55/230V BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

**General ordering data**

Version	Filter fan, IP55, black
Order No.	<a href="#">2556940000</a>
Type	FF 66 55/230V BK
GTIN (EAN)	4050118567564
Qty.	1 pc(s).

## FF 66 55/230V BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	157 mm	Depth (inches)	6.181 inch
Height	320 mm	Height (inches)	12.598 inch
Width	320 mm	Width (inches)	12.598 inch
Net weight	3,200 g		

## Temperatures

Operating temperature range	-40...55 °C
-----------------------------	-------------

## General data

Colour	black		
Current consumption	Mains frequency	50 Hz	
	Current	0.53 A	
	Mains frequency	60 Hz	
	Current	0.72 A	
EMC version	No		
Fan type	Roof fan		
Filter class	G 4		
Fuse	6 A		
Height of installation cut-outs	291 mm		
MTBF	40,000 h		
Mounting depth	150 mm		
Mounting height	7 mm		
Noise emission	63 dB(A)		
Operating temperature range	-40...55 °C		
Power	Mains frequency	50 Hz	
	nominal	120 W	
	Mains frequency	60 Hz	
	nominal	160 W	
Protection class (UL)	Type 12		
Rated voltage	230 V AC $\pm$ 10%		
Size	6		
Type of connection	Spring contact		
Type of mounting	Snap-on		
UL 94 flammability rating	V-0		
UV-resistant	Yes		
Volume flow with exhaust filter	Mains frequency	50 Hz	
	Volume flow	490 m³/h	
	Exhaust filter	IP55	
	Mains frequency	60 Hz	
	Volume flow	501 m³/h	
	Exhaust filter	IP55	
Volume flow, free-blowing	Mains frequency	50 Hz	
	Volume flow	770 m³/h	
	Mains frequency	60 Hz	
	Volume flow	785 m³/h	
Volume flow, free-blowing at 50 Hz	770 m³/h		
Volume flow, free-blowing at 60 Hz	785 m³/h		
Width of installation cut-outs	291 mm		
With filter	Yes		
With protective cover	Yes		

## FF 66 55/230V BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

## Classifications

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ECLASS 9.1	27-18-07-16	ECLASS 10.0	27-18-07-16
ECLASS 11.0	27-18-07-16	ECLASS 12.0	27-18-07-16
ECLASS 13.0	27-18-07-16		

## Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (cURus)	E252704

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
User Documentation	<a href="#">Installation- and operating instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>


## FF 66 55/230V BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany


[www.weidmueller.com](http://www.weidmueller.com)

# Drawings

## Graph



## Graph



## FF 66 55/230V BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Filter fan



The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

## General ordering data

Type	FF-FIMT 6X 54	Version
Order No.	<a href="#">2567310000</a>	Filter mat, IP54, white
GTIN (EAN)	4050118576955	
Qty.	5 pc(s).	
Type	FF-FIMT 6X 55	Version
Order No.	<a href="#">2557050000</a>	Filter mat, IP55, white
GTIN (EAN)	4050118567687	
Qty.	5 pc(s).	

## Exhaust filter



The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats. Thought out details as the functional flap cover enable a fast and tool-less change of the filter mats which saves time and money.

## General ordering data

Type	EF 60 54 GY	Version
Order No.	<a href="#">2557210000</a>	Exhaust filter, IP54, grey
GTIN (EAN)	4050118567847	
Qty.	1 pc(s).	
Type	EF 60 55 GY	Version
Order No.	<a href="#">2557230000</a>	Exhaust filter, IP55, grey
GTIN (EAN)	4050118567861	
Qty.	1 pc(s).	
Type	EF 60 54 BK	Version
Order No.	<a href="#">2557220000</a>	Exhaust filter, IP54, black
GTIN (EAN)	4050118567854	
Qty.	1 pc(s).	
Type	EF 60 55 BK	Version
Order No.	<a href="#">2557240000</a>	Exhaust filter, IP55, black
GTIN (EAN)	4050118567878	
Qty.	1 pc(s).	