

**RFF-FIMT 607/610 54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

The filter fans combine a safe and profitable cabinet cooling due to their low energy consumption by maximum air flow. The fluted filter mat of the IP 55 version extends the service life by up to 300% in comparison to conventional filter mats.

**General ordering data**

Version	Filter mat, IP54, white
Order No.	<a href="#">2557790000</a>
Type	RFF-FIMT 607/610 54
GTIN (EAN)	4050118568431
Qty.	20 pc(s).

**RFF-FIMT 607/610 54****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Height	95 mm	Height (inches)	3.74 inch
Width	290 mm	Width (inches)	11.417 inch
Net weight	19.2 g		

**Temperatures**

Operating temperature range	-15...55 °C
-----------------------------	-------------

**General data**

Colour	white	Filter class	G 4
Operating temperature range	-15...55 °C	Protection class (UL)	Type 12
Type of mounting	Snap-on	With filter	Yes

**Classifications**

ETIM 6.0	EC000320	ETIM 7.0	EC000320
ETIM 8.0	EC000320	ETIM 9.0	EC000320
ECLASS 9.1	27-18-07-16	ECLASS 10.0	27-18-07-16
ECLASS 11.0	27-18-07-16	ECLASS 12.0	27-18-07-16
ECLASS 13.0	27-18-07-16		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">Operating instructions</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>