

CABTITE LNS M63 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

A kép illusztráció



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Általános rendelési adatok

| | |
|----------------|--|
| Verzió | leválasztható ellenanya, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 72 mm, Szélesség: 72 mm, Mélység: 7 mm, -40 °C...120 °C |
| Rendelési szám | 2584010000 |
| Típus | CABTITE LNS M63 BK |
| GTIN (EAN) | 4050118617245 |
| Qty. | 5 Stück |

CABTITE LNS M63 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Műszaki adatok

Méretetek és tömegek

| | | | |
|-----------|-------|------------------|------------|
| Mélység | 7 mm | Mélység (coll) | 0,276 inch |
| Magasság | 72 mm | Magasság (coll) | 2,835 inch |
| Szélesség | 72 mm | Szélesség (coll) | 2,835 inch |
| Átmérő | 83 mm | Nettó tömeg | 9,2 g |

Hőmérsékletek

| | |
|-------------------|-----------------|
| Üzemi hőmérséklet | -40 °C...120 °C |
|-------------------|-----------------|

General information

| | | | |
|--------------------------|------------------------------|--------------|-------|
| AF 1. méret | 72 mm | AF 2. méret | 83 mm |
| Anyag | Poliamid, üvegszál-erősítésű | Halogén | Nem |
| Külső menet | M 63 | Menet hossza | 7 mm |
| Menetemelkedés | 1,5 mm | Szilikon | Nem |
| UL 94 éghetőségi osztály | V-0 | | |

Besorolások

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000940 | ETIM 7.0 | EC000940 |
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ECLASS 9.0 | 27-14-44-24 | ECLASS 9,1 | 27-14-44-24 |
| ECLASS 10.0 | 27-14-44-24 | ECLASS 11.0 | 27-14-44-24 |
| ECLASS 12.0 | 27-14-08-07 | ECLASS 13.0 | 27-14-08-07 |

Tanúsítványok

| | |
|------|----------|
| ROHS | Megfelel |
|------|----------|

Letöltések

| | |
|--------------------|---|
| Engineering Data | CAD data – STEP |
| User Documentation | Installation Instructions |
| Katalógusok | Catalogues in PDF-format |

CABTITE LNS M63 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Rajzok****Méretrajz**