

## CABTITE LNS M32 BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## A kép illusztráció



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

## Általános rendelési adatok

Verzió	leválasztható ellenanya, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 40 mm, Szélesség: 40 mm, Mélység: 7 mm, -40 °C...120 °C
Rendelési szám	<a href="#">2584070000</a>
Típus	CABTITE LNS M32 BK
GTIN (EAN)	4050118616446
Qty.	10 Stück

## CABTITE LNS M32 BK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Műszaki adatok

## Méretetek és tömegek

Mélység	7 mm	Mélység (coll)	0,276 inch
Magasság	40 mm	Magasság (coll)	1,575 inch
Szélesség	40 mm	Szélesség (coll)	1,575 inch
Átmérő	45 mm	Nettó tömeg	4,2 g

## Hőmérsékletek

Üzemi hőmérséklet	-40 °C...120 °C
-------------------	-----------------

## General information

AF 1. méret	40 mm	AF 2. méret	45 mm
Anyag	Poliamid, üvegszál-erősítésű	Halogén	Nem
Külső menet	M 32	Menet hossza	7 mm
Menetemelkedés	1,5 mm	Szilikon	Nem
UL 94 éghetőségi osztály	V-0		

## Besorolások

ETIM 6.0	EC000940	ETIM 7.0	EC000940
ETIM 8.0	EC000940	ETIM 9.0	EC000940
ECLASS 9.0	27-14-44-24	ECLASS 9,1	27-14-44-24
ECLASS 10.0	27-14-44-24	ECLASS 11.0	27-14-44-24
ECLASS 12.0	27-14-08-07	ECLASS 13.0	27-14-08-07

## Tanúsítványok

ROHS	Megfelel
------	----------

## Letöltések

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Installation Instructions</a>
Katalógusok	<a href="#">Catalogues in PDF-format</a>

## CABTITE LNS M32 BK

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Rajzok

### Méretrajz

