

**CBC-SP 14-120/25 V2 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

Version	Protective cable hose coil
Order No.	<a href="#">2588620000</a>
Type	CBC-SP 14-120/25 V2 WT
GTIN (EAN)	4050118602128
Qty.	25 m

**CBC-SP 14-120/25 V2 WT****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Length	100,000 mm	Length (inches)	3,937 inch
Diameter	12 mm	Net weight	31.92 g

**Temperatures**

Operating temperature range	-15...60 °C
-----------------------------	-------------

**General information**

Bundle diameter, max.	120 mm	Bundle diameter, min.	14 mm
Colour	white	Diameter	12 mm
Material	Polyethylene	Nominal diameter	9.6 mm
Operating temperature range	-15...60 °C	UL 94 flammability rating	V-2
Usable cross-section	11,309 mm <sup>2</sup>		

**Classifications**

ETIM 6.0	EC001182	ETIM 7.0	EC001182
ETIM 8.0	EC001182	ETIM 9.0	EC001182
ECLASS 9.1	27-43-03-03	ECLASS 10.0	27-43-03-03
ECLASS 11.0	27-43-03-03	ECLASS 12.0	27-43-03-03
ECLASS 13.0	27-43-03-03		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--