

**CBC-SP 2-12/50 TP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Protective cable hose coil |
| Order No.  | <a href="#">2588830000</a> |
| Type       | CBC-SP 2-12/50 TP          |
| GTIN (EAN) | 4050118600346              |
| Qty.       | 50 m                       |

**CBC-SP 2-12/50 TP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|          |            |                 |             |
|----------|------------|-----------------|-------------|
| Length   | 400,000 mm | Length (inches) | 15,748 inch |
| Diameter | 3 mm       | Net weight      | 5.38 g      |

**Temperatures**

|                             |             |
|-----------------------------|-------------|
| Operating temperature range | -15...60 °C |
|-----------------------------|-------------|

**General information**

|                             |              |                       |                     |
|-----------------------------|--------------|-----------------------|---------------------|
| Bundle diameter, max.       | 12 mm        | Bundle diameter, min. | 2 mm                |
| Colour                      | Transparent  | Diameter              | 3 mm                |
| Material                    | Polyethylene | Nominal diameter      | 1.5 mm              |
| Operating temperature range | -15...60 °C  | Usable cross-section  | 113 mm <sup>2</sup> |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001182    | ETIM 7.0    | EC001182    |
| ETIM 8.0    | EC001182    | ETIM 9.0    | EC001182    |
| ECLASS 9.1  | 27-43-03-03 | ECLASS 10.0 | 27-43-03-03 |
| ECLASS 11.0 | 27-43-03-03 | ECLASS 12.0 | 27-43-03-03 |
| ECLASS 13.0 | 27-43-03-03 |             |             |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|