

**HDC MRJ45 GC F****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

Version	RJ45 module, RJ45 Gender Changer
Order No.	<a href="#">2592030000</a>
Type	HDC MRJ45 GC F
GTIN (EAN)	4050118600506
Qty.	1 pc(s).

## HDC MRJ45 GC F

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Depth	34 mm	Depth (inches)	1.339 inch
Width	14.5 mm	Width (inches)	0.571 inch
Net weight	5.5 g		

## Temperatures

Limit temperature	-40 °C ... 70 °C
-------------------	------------------

## General data

Insulation strength	$10^{12} \Omega$	Material	Polycarbonate, glass fibre reinforced
Number of poles	8	Plugging cycles	750 (RJ45)
Pollution severity	3	Rated current (DIN EN 61984)	1 A
Rated impulse voltage (DIN EN 61984)	0.8 kV	Rated voltage (DIN EN 61984)	50 V
Required plug-in slots	1	Series	ModuPlug
Surge voltage category	III	Type	Female
UL 94 flammability rating	V-0		

## Classifications

ETIM 6.0	EC002312	ETIM 7.0	EC002312
ETIM 8.0	EC002312	ETIM 9.0	EC002312
ECLASS 9.0	27-44-02-92	ECLASS 9.1	27-44-02-18
ECLASS 10.0	27-44-02-92	ECLASS 11.0	27-44-02-92
ECLASS 12.0	27-44-02-92	ECLASS 13.0	27-44-02-92

## Environmental Product Compliance

REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	b0a2f8e6-c50c-4c56-9381-cc6543281fbb

## Approvals

Approvals



UL File Number Search	UL Website
Certificate No. (cURus)	E92202

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's declaration</a>
Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>