

P BAG XL SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | |
|------------|----------------------------|
| Version | Tools, Accessories |
| Order No. | 2602170000 |
| Type | P BAG XL SET 7 |
| GTIN (EAN) | 4050118613155 |
| Qty. | 1 pc(s). |

P BAG XL SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

| | | | |
|------------|---------|-----------------|-------------|
| Depth | 220 mm | Depth (inches) | 8.661 inch |
| Height | 60 mm | Height (inches) | 2.362 inch |
| Width | 320 mm | Width (inches) | 12.598 inch |
| Net weight | 1,960 g | | |

Technical data

| | |
|------------------------|-----------------|
| Description of article | Toolbag, fitted |
|------------------------|-----------------|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000181 | ETIM 7.0 | EC000181 |
| ETIM 8.0 | EC000181 | ETIM 9.0 | EC000181 |
| ECLASS 9.0 | 21-10-01-90 | ECLASS 9.1 | 21-10-01-90 |
| ECLASS 10.0 | 21-10-01-90 | ECLASS 11.0 | 21-10-01-90 |
| ECLASS 12.0 | 21-10-01-90 | ECLASS 13.0 | 21-10-01-90 |

Environmental Product Compliance

| | |
|------------|--------------------------------------|
| REACH SVHC | Lead 7439-92-1 |
| SCIP | 1eacbb3e-7931-4ebb-9179-f29fd9b50028 |

Downloads

| | |
|------------|--|
| Catalogues | Catalogues in PDF-format |
|------------|--|

P BAG XL SET 7

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Slotted screwdriver



VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| Type | SDIS SLIM 0.6X3.5X100 | Version |
|------------|----------------------------|---|
| Order No. | 2749610000 | Mounting tool, Blade width (B): 3.5 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896350 | thickness (A): 0.6 mm |
| Qty. | 1 pc(s). | |
| Type | SDIS SLIM 0.8X4.0X100 | Version |
| Order No. | 2749620000 | Mounting tool, Blade width (B): 4 mm, Blade length: 100 mm, Blade |
| GTIN (EAN) | 4050118896367 | thickness (A): 0.8 mm |
| Qty. | 1 pc(s). | |

Crimping tools



Crimping tools for wire end ferrules, with and without plastic collars

- Ratchet guarantees precise crimping
- Release option in the event of incorrect operation

General ordering data

| Type | PZ 6 ROTO L | Version |
|------------|----------------------------|--|
| Order No. | 1444050000 | Pressing tool, Crimping tool for wire-end ferrules, 0.14mm ² , 6mm ² , |
| GTIN (EAN) | 4050118248593 | Trapezoidal crimp |
| Qty. | 1 pc(s). | |

P BAG XL SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****unfitted**

Workshops and factories prefer well-organised sets of tools. That results in minimal searching and preparation, and that saves money. Weidmüller implements such knowledge when combining products, characterised by good benefits for users and good functionality. Weidmüller Crimp Sets for cutting, stripping and crimping wire end ferrules provide users with practical toolkits.

General ordering data

| | | |
|------------|----------------------------|--------------------|
| Type | P BAG BIG | Version |
| Order No. | 2576620000 | Tools, Accessories |
| GTIN (EAN) | 4050118650594 | |
| Qty. | 1 pc(s). | |

with LCD Display

The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LCD-Display
- acc. to VDE standard,
- high peak voltage strength
- the right tester for every application

General ordering data

| | | |
|------------|----------------------------|--------------------------------------|
| Type | VT DIGI PRO | Version |
| Order No. | 9918870000 | Testing tools, 2-pole voltage tester |
| GTIN (EAN) | 4032248405756 | |
| Qty. | 1 pc(s). | |

P BAG XL SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Cutting tools**

Cutting tools for conductors up to 8 mm, 12 mm, 14 mm and 22 mm outside diameter. The special blade geometry allows pinch-free cutting of copper and aluminium conductors with minimum physical effort. The cutting tools (KT 8 to KT 22) also come with VDE and GS-tested protective insulation up to 1,000 V in accordance with EN/IEC 60900.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | KT 8 | Version |
| Order No. | 9002650000 | Cutting tools, Cutting tool for one-hand operation |
| GTIN (EAN) | 4008190020163 | |
| Qty. | 1 pc(s). | |

Tools

Sheathing stripper for PVC cables

**General ordering data**

| | | |
|------------|----------------------------|----------------------------|
| Type | AM 25 | Version |
| Order No. | 9001540000 | Tools, Sheathing strippers |
| GTIN (EAN) | 4008190138271 | |
| Qty. | 1 pc(s). | |

P BAG XL SET 7**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories**Tools**

- Stripping tools with automatic self-adjustment
- For flexible and solid conductors
- Ideally suitable for mechanical and plant engineering, railway and rail traffic, wind energy, robot technology, explosion protection as well as marine, offshore and ship building sectors
- Stripping length adjustable via end stop
- Automatic opening of clamping jaws after stripping
- No fanning-out of individual conductors
- Adjustable to diverse insulation thicknesses
- Double-insulated cables in two process steps without special adjustment
- No play in self-adjusting cutting unit
- Long service life
- Optimised ergonomic design

General ordering data

| | | |
|------------|----------------------------|-----------------------------------|
| Type | STRIPAX ULTIMATE | Version |
| Order No. | 1468880000 | Tools, Stripping and cutting tool |
| GTIN (EAN) | 4050118274158 | |
| Qty. | 1 pc(s). | |

Crosshead screwdriver, Phillips

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

| | | |
|------------|----------------------------|--|
| Type | SDIK SLIM PH1 X 80 | Version |
| Order No. | 2749650000 | Screwdriver, Blade width (B): 1 mm, 80 mm, Blade thickness (A): 1 |
| GTIN (EAN) | 4050118896398 | |
| Qty. | 1 pc(s). | |
| Type | SDIK SLIM PH2 X 100 | Version |
| Order No. | 2749660000 | Screwdriver, Blade width (B): 2 mm, 100 mm, Blade thickness (A): 2 |
| GTIN (EAN) | 4050118896404 | |
| Qty. | 1 pc(s). | |