

H0,5/16DS W BD GSP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

- Linked wire-end ferrules on reel (5,000 pcs.)
- Weidmüller colour code
- DIN colour code

General ordering data

Version	Wire-end ferrule, Standard, 12 mm, 10 mm, white
Order No.	2604630000
Type	H0,5/16DS W BD GSP
GTIN (EAN)	4050118649437
Qty.	4,000 pc(s).

H0,5/16DS W BD GSP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Dimensions and weights**

Net weight	0.124 g
------------	---------

Technical data

Description of article	Wire end ferrules on reel, white	Version	Standard
------------------------	----------------------------------	---------	----------

Wire-end ferrules

Collar diameter (D2)	2.9 mm	Colour code	DIN
Conductor cross-section	0.5 mm ²	Contact surface diameter (D1)	1 mm
Contact surface length (L2)	10 mm	L1 in mm	16 mm
Metal sleeve thickness (S1)	0.15 mm	Plastic collar thickness (S2)	0.25 mm
Stripping length	12 mm	Wire connection cross section AWG, max.	AWG 20

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
ETIM 8.0	EC000005	ETIM 9.0	EC000005
ECLASS 9.0	27-40-02-01	ECLASS 9.1	27-40-02-01
ECLASS 10.0	27-40-02-01	ECLASS 11.0	27-40-02-01
ECLASS 12.0	27-40-02-01	ECLASS 13.0	27-40-02-01

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E354986

Downloads

User Documentation	Technical information - EN Technical information - DE
Catalogues	Catalogues in PDF-format

H0,5/16DS W BD GSP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

