


**FBCON PA CG/M12 4WAY LIMITER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

**Functionality**

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

**General ordering data**

Version	, 4-channel distributor LIMITER, IP66, IP67, Branch line M12
Order No.	<a href="#">2617200000</a>
Type	FBCON PA CG/M12 4WAY LIMITER
GTIN (EAN)	4050118621723
Qty.	1 pc(s).

## FBCON PA CG/M12 4WAY LIMITER

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Height	34 mm	Height (inches)	1.339 inch
Width	125 mm	Width (inches)	4.921 inch
Length	80 mm	Length (inches)	3.15 inch
Net weight	660 g		

## Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

## Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable entry	Branch line M12
Cable glands	Brass cable gland	Connection type PE	M12 spur line
Current limiting	adjustable, 20 mA, 40 mA, 60 mA	Design of housing	With pressure compensation element
Housing main material	Aluminium, AlSi12, Aluminium	Housing surface	powder coating
Operating voltage $U_{max}$ , max.	32 V	Pollution severity	3
Protection degree	IP66, IP67	Type of distribution	4-channel distributor LIMITER
Type of mounting	surface-mounted		

## Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

## Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

## Approvals

Approvals



UL File Number Search	UL Website
Certificate no. (cULus)	E141197

## Downloads

Approval/Certificate/Document of Conformity	<a href="#">Declaration of Conformity</a>
Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">Instruction sheet</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

## FBCON PA CG/M12 4WAY LIMITER

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

