


**HS-FR 1.2-2.4/25 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

|                    |  |
|--------------------|--|
| Version            | Conductor and cable markers, 1.2 - 2.4 mm, 24.9 x 4 mm, yellow |
| Order No.          | <a href="#">2621570000</a>                                     |
| Type               | HS-FR 1.2-2.4/25 MM Y  |
| GTIN (EAN)         | 4050118625479  |
| Qty.               | 2,000 pc(s).   |
| compatible printer | <a href="#">2599430000</a> <a href="#">2599440000</a>          |

**HS-FR 1.2-2.4/25 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 0.77 mm | Depth (inches)  | 0.03 inch  |
| Height     | 24.9 mm | Height (inches) | 0.98 inch  |
| Width      | 4 mm    | Width (inches)  | 0.157 inch |
| Net weight | 0.252 g |                 |            |

**Temperatures**

|                             |              |
|-----------------------------|--------------|
| Operating temperature range | -55...125 °C |
|-----------------------------|--------------|

**General data**

|                                   |             |                                   |              |
|-----------------------------------|-------------|-----------------------------------|--------------|
| Colour                            | yellow      | Halogen                           | No           |
| Material                          | Polyolefine | Operating temperature range       | -55...125 °C |
| Operating temperature range, max. | 125 °C      | Operating temperature range, min. | -55 °C       |
| Size of labelling field           | 4 x 24.9 mm | Width                             | 4 mm         |

**Conductor and cable markers**

|   |                      |   |                            |
|---|----------------------|---|----------------------------|
| Conductor O.D.                          | 1.2 - 2.4 mm         | Conductor O.D., max.                    | 2.4 mm                     |
| Conductor O.D., min.                    | 1.2 mm               | Conductor cross-section, max.           | 0.5 mm <sup>2</sup>        |
| Conductor cross-section, min.           | 0.25 mm <sup>2</sup> | Cross-section for connected wire        | 0.25 - 0.5 mm <sup>2</sup> |
| Halogen                                 | No                   | Rate of shrinkage                       | 2:1                        |
| Recommended shrinking temperature       | 90 °C                | Wire connection cross section AWG, max. | AWG 20                     |
| Wire connection cross section AWG, min. | AWG 24               |   |                            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001530    | ETIM 7.0    | EC001530    |
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ECLASS 9.0  | 27-40-04-01 | ECLASS 9.1  | 27-40-04-01 |
| ECLASS 10.0 | 27-40-04-01 | ECLASS 11.0 | 27-28-11-02 |
| ECLASS 12.0 | 27-28-11-02 | ECLASS 13.0 | 27-28-11-02 |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**


|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|

**HS-FR 1.2-2.4/25 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



**HS-FR 1.2-2.4/25 MM Y**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****THM MULTIMARK**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Type       | THM MMP ROLLER 115         |
| Order No.  | <a href="#">1357420000</a> |
| GTIN (EAN) | 4050118160314              |
| Qty.       | 1 pc(s).                   |

**Ink ribbons**

These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

**General ordering data**

|            |                            |            |
|------------|----------------------------|------------|
| Type       | RIBBON MM-HS 60/300 SW     | Version    |
| Order No.  | <a href="#">2448880000</a> | Ink ribbon |
| GTIN (EAN) | 4050118462944              |            |
| Qty.       | 1 pc(s).                   |            |

### HS-FR 1.2-2.4/25 MM Y

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

### THM MULTIMARK PLUS



These printers produce excellent printing results thanks to the thermal transfer technique. Different materials and the user-friendly printing system under Windows optimise marking efforts.

### General ordering data

|            |                            |
|------------|----------------------------|
| Type       | MM PLUS ROLLER 110         |
| Order No.  | <a href="#">2672590000</a> |
| GTIN (EAN) | 4050118708097              |
| Qty.       | 1 pc(s).                   |