


**HS-FR 12.7-25.4/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The heat-shrinkable sleeve is printable on 2 sides and can be used for marking and insulating cables and wires. The flexible, heat-shrink material enables a firm, perfect fit around the conductor and therefore saves space.

**General ordering data**

Version	Conductor and cable markers, 12.7 - 25.4 mm, 49.8 x 40.5 mm, yellow
Order No.	<a href="#">2621890000</a>
Type	HS-FR 12.7-25.4/50 MM Y
GTIN (EAN)	4050118625158
Qty.	300 pc(s).
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

**HS-FR 12.7-25.4/50 MM Y****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

Depth	0.77 mm	Depth (inches)	0.03 inch
Height	49.8 mm	Height (inches)	1.961 inch
Width	40.5 mm	Width (inches)	1.594 inch
Net weight	1.6 g		

**Temperatures**

Operating temperature range	-55...125 °C
-----------------------------	--------------

**General data**

Colour	yellow	Halogen	No
Material	Polyolefine	Operating temperature range	-55...125 °C
Operating temperature range, max.	125 °C	Operating temperature range, min.	-55 °C
Size of labelling field	40.5 x 49.8 mm	Width	40.5 mm

**Conductor and cable markers**

Conductor O.D.	12.7 - 25.4 mm	Conductor O.D., max.	25.4 mm
Conductor O.D., min.	12.7 mm	Conductor cross-section, max.	120 mm <sup>2</sup>
Conductor cross-section, min.	35 mm <sup>2</sup>	Cross-section for connected wire	35 - 120 mm <sup>2</sup>
Halogen	No	Rate of shrinkage	2:1
Recommended shrinking temperature	90 °C	Wire connection cross section AWG, max.	AWG 4/0
Wire connection cross section AWG, min.	AWG 2		

**Classifications**

ETIM 6.0	EC001530	ETIM 7.0	EC001530
ETIM 8.0	EC001530	ETIM 9.0	EC001530
ECLASS 9.0	27-40-04-01	ECLASS 9.1	27-40-04-01
ECLASS 10.0	27-40-04-01	ECLASS 11.0	27-28-11-02
ECLASS 12.0	27-28-11-02	ECLASS 13.0	27-28-11-02

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--

### HS-FR 12.7-25.4/50 MM Y

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

