


FBCON PA CG 1WAY LIMITER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

For standard industrial applications (non-hazardous areas), PROFIBUS PA junction boxes and limiters are available as 1-way, 2-way, 4-way, and 8-way distributors. FBCon limiters are designed to protect connected field devices from over voltages and short circuits. As voltage-limiting protective elements, suppressor diodes are used. Due to the integrated current limitation, the segment is also protected against short circuit on a spur line. EMC cable glands, protection class IP66 and a wide operating temperature range safely protect your connections in harsh environments.

Functionality

- EMC cable glands for trunk and spurs
- M12 connector for spurs
- External earthing stud
- Pressure equalizing element
- Protection class IP66
- Aluminium and stainless-steel versions
- Profibus PA / Foundation Fieldbus compatible

Note: The use of FBCon products with aluminum enclosures and / or M12 connectors is not recommended in strongly saline environments.

General ordering data

Version	, 1-channel distributor LIMITER, IP66, IP67
Order No.	2623870000
Type	FBCON PA CG 1WAY LIMITER
GTIN (EAN)	4050118627381
Qty.	1 pc(s).

FBCON PA CG 1WAY LIMITER

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	34 mm	Height (inches)	1.339 inch
Width	64 mm	Width (inches)	2.52 inch
Length	58 mm	Length (inches)	2.283 inch
Net weight	266 g		

Temperatures

Storage temperature	-40 °C...80 °C	Operating temperature	-40 °C...75 °C
---------------------	----------------	-----------------------	----------------

Technical data

Bus system	Profibus-PA, Foundation Fieldbus	Cable glands	Brass cable gland
Connection type PE	Spur line with cable gland	Current limiting	adjustable, 20 mA, 40 mA, 60 mA
Design of housing	With pressure compensation element	Housing main material	Aluminium, AISi12, Aluminum
Housing surface	powder coating	Number of poles	3
Operating voltage U_{max} , max.	32 V	Pollution severity	3
Protection degree	IP66, IP67	Type of distribution	1-channel distributor LIMITER
Type of mounting	surface-mounted		

Classifications

ETIM 6.0	EC001604	ETIM 7.0	EC001604
ETIM 8.0	EC001604	ETIM 9.0	EC001604
ECLASS 9.0	27-24-26-08	ECLASS 9.1	27-24-26-08
ECLASS 10.0	27-24-26-08	ECLASS 11.0	27-24-26-08
ECLASS 12.0	27-44-01-11	ECLASS 13.0	27-44-01-11

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Approvals

Approvals



UL File Number Search	UL Website
Certificate no. (cULus)	E141197

Downloads


Approval/Certificate/Document of Conformity	Declaration of Conformity
Engineering Data	CAD data – STEP
User Documentation	Instruction sheet
Catalogues	Catalogues in PDF-format

FBCON PA CG 1WAY LIMITER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



DIP switches

1	2	Current
		20 mA
		40 mA
		60 mA

A → PA-
S → Shield
B → PA+

