

## FP ENC DR07 230 3C P

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Extensive range of accessories for the FieldPower® boxes.  
Cable seals, terminal rails, locking elements and much more.

### General ordering data

Version	Field Power® terminal rail, Steel, galvanized, 230 mm, for plastic lid
Order No.	<a href="#">2633520000</a>
Type	FP ENC DR07 230 3C P
GTIN (EAN)	4050118664386
Qty.	5 pc(s).

Creation date May 10, 2024 9:08:38 PM CEST

Catalogue status 04.05.2024 / We reserve the right to make technical changes.

## FP ENC DR07 230 3C P

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technical data

### Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	230 mm	Width (inches)	9.055 inch
Net weight	83.4 g		

### Temperatures

Operating temperature	-40 °C...85
-----------------------	-------------

### General specifications

Installation advice	Screws included	Insulating material	Steel
Material	Steel, galvanized	Colour	silver

### General data

Material	Steel, galvanized	Insulating material	Steel
Colour	silver	Type of mounting	Screw mounting
Mounting position, installation notice	for plastic lid	Installation advice	Screws included
Version	with slot		

### Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ETIM 9.0	EC001285
ECLASS 9.0	27-40-06-02	ECLASS 9.1	27-40-06-02
ECLASS 10.0	27-40-06-02	ECLASS 11.0	27-40-06-02
ECLASS 12.0	27-40-06-02	ECLASS 13.0	27-40-06-02

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	42d748fc-bbd3-41cb-951a-c952873e955b

### Approvals

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">Manufacturer's Declaration FieldPower® Enclosure parts</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Data sheet**

**FP ENC DR07 230 3C P**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**



## FP ENC DR07 230 3C P

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Bits E6,3 - Torx®



The Weidmüller bits are standard bits which are highly popular with users thanks to their good quality, large range and efficiency. The computer-controlled hardening method enables Weidmüller to guarantee a consistently high standard of quality.

The high-quality raw materials used make it possible to reach torques far higher than any of those specified in the relevant DIN standards:

- DIN 5261 for PH/PZ bits,
- DIN 5263 for slotted bits,
- Camcar standard for TORX bits

That means a long life at high torques and hence ideal conditions for standard situations.

**The benefits:**

- Suitable for all types of screws. Because of their excellent hardness values of 59-61 HRC, they are suitable for use with both manual and power tools.
- Good wearing resistance and thus a long life expectancy.
- Optimum fit in all DIN screws means low wear and optimum torque transmission.
- Manufactured to meet professional quality criteria according to relevant ISO standards with a consistently high standard of quality.

**General ordering data**

Type	BIT E6,3 T20 X 150	Version
Order No.	<a href="#">2821510000</a>	Mounting tool
GTIN (EAN)	4064675359050	
Qty.	50 pc(s).	

**DMS PRO**

Weidmüller torque screwdrivers have an ergonomic design and are therefore ideal for use with one hand. They can be used without causing fatigue in all installation positions. Apart from that, they incorporate an automatic torque limiter and have a good reproducibility accuracy.

**General ordering data**

Type	DMS PRO	Version
Order No.	<a href="#">1479120000</a>	Mounting tool
GTIN (EAN)	4050118287011	
Qty.	1 pc(s).	