

ZQV 35N/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image****Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

Version	Cross-connector (terminal), Plugged, Number of poles: 2, Pitch in mm (P): 16.00, 125 A, orange
Order No.	2634950000
Type	ZQV 35N/2
GTIN (EAN)	4050118694208
Qty.	10 pc(s).

ZQV 35N/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	6 mm	Depth (inches)	0.236 inch
Height	43.4 mm	Height (inches)	1.709 inch
Width	25 mm	Width (inches)	0.984 inch
Net weight	17 g		

Temperatures

Storage temperature	-25 °C...55 °C	Operating temperature	-60 °C...130 °C
Continuous operating temp., min.	-60	Continuous operating temp., max.	130

Material data

Material	Wemid	Colour	orange
UL 94 flammability rating	V-0		

System specifications

Version	For the terminals
---------	-------------------

Additional technical data

Installation advice	Direct mounting	Type of fixing	Plugged
Type of mounting	Plugged		

Dimensions

Pitch in mm (P)	16 mm
-----------------	-------

General

Installation advice	Direct mounting	Number of poles	2
---------------------	-----------------	-----------------	---

Rating data

Rated current	125 A
---------------	-------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ETIM 9.0	EC000489
ECLASS 9.0	27-14-11-40	ECLASS 9.1	27-14-11-40
ECLASS 10.0	27-14-11-40	ECLASS 11.0	27-14-11-40
ECLASS 12.0	27-14-11-40	ECLASS 13.0	27-25-03-03

Downloads

Approval/Certificate/Document of Conformity	Confirmation of Standards EN 45545-2_2020-10
Engineering Data	CAD data – STEP
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format